



# UL LISTED MAGLOCKS

## MAGLOCKS WITH ADJUSTABLE RELOCK TIME DELAY & LOCK STATUS SENSOR



### PRIMARY APPLICATIONS



### DESCRIPTION

BEA's UL Listed Maglocks provide a standards compliant locking solution for retail, healthcare, banking and other high security facilities that require UL Listed security products. Maglocks can be used on hollow metal, wood, aluminum, glass and composite door materials.

The UL Listed Maglocks are available in surface mount single or double door configurations, with holding force of 600 or 1,200 lbs. These locks include adjustable 0 – 90 second relock time delay and a lock status sensor with visible LED.

### FEATURES & BENEFITS

- UL Listed
- Adjustable 0 – 90 second relock time delay
- Lock status sensor with visible LED
- Lock status sensor offers either normally open (NO) or normally closed (NC) output configurations
- Input voltage of 12 / 24 VDC, must be used with UL Listed power supply
- Variety of mounting hardware available
- Available in access control packages with request-to-exit sensor, logic module, actuator, power supply and maglock



BEA, Inc.  
RIDC Park West  
100 Enterprise Drive  
Pittsburgh, PA 15275-1213

Customer Service: 800.523.2462  
Technical Support: 800.407.4545  
[www.BEAinc.com](http://www.BEAinc.com)

## TECHNICAL SPECIFICATIONS

### 10MAGLOCK3UL

<b>Door Configuration</b>	Single, surface mount
<b>Holding Force</b>	600 lb
<b>Input Voltage</b>	12 / 24 VDC (UL Listed power supply required)
<b>Current Draw</b>	0.50 A @ 12 VDC 0.25 A @ 24 VDC
<b>Dimensions</b>	9.84 in (W) × 1.65 in (H) × 1.02 in (D)
<b>Material</b>	Anodized Aluminum housing
<b>Relock Time Delay</b>	0 s – 90 s
<b>Sensor</b>	Lock Status Sensor (NO or NC outputs)
<b>Output Relay</b>	Up to 1 A @ 24 VDC

### 10MAGLOCK6UL

<b>Door Configuration</b>	Double, surface mount
<b>Holding Force</b>	600 lb
<b>Input Voltage</b>	12 / 24 VDC (UL Listed power supply required)
<b>Current Draw</b>	1 A @ 12 VDC 0.50 A @ 24 VDC
<b>Dimensions</b>	19.76 in (W) × 1.65 in (H) × 1.02 in (D)
<b>Material</b>	Anodized Aluminum housing
<b>Relock Time Delay</b>	0 s – 90 s
<b>Sensor</b>	Lock Status Sensor (NO or NC outputs)
<b>Output Relay</b>	Up to 1 A @ 24 VDC

### 10MAGLOCK1UL

<b>Door Configuration</b>	Single, surface mount
<b>Holding Force</b>	1200 lb
<b>Input Voltage</b>	12 / 24 VDC (UL Listed power supply required)
<b>Current Draw</b>	0.50 A @ 12 VDC 0.30 mA @ 24 VDC
<b>Dimensions</b>	10.47 in (W) × 2.87 in (H) × 1.58 in (D)
<b>Material</b>	Anodized Aluminum housing
<b>Relock Time Delay</b>	0 s – 90 s
<b>Sensor</b>	Lock Status Sensor (NO or NC outputs)
<b>Output Relay</b>	Up to 1 A @ 24 VDC

### 10MAGLOCK5UL

<b>Door Configuration</b>	Double, surface mount
<b>Holding Force</b>	1200 lb
<b>Input Voltage</b>	12 / 24 VDC (UL Listed power supply required)
<b>Current Draw</b>	1 A @ 12 VDC 0.60 A @ 24 VDC
<b>Dimensions</b>	20.94 in (W) × 2.87 in (H) × 1.58 in (D)
<b>Material</b>	Anodized Aluminum housing
<b>Relock Time Delay</b>	0 s – 90 s
<b>Sensor</b>	Lock Status Sensor (NO or NC outputs)
<b>Output Relay</b>	Up to 1 A @ 24 VDC

## RELATED PRODUCTS



**10MAGLOCK3UL**  
600 LB, SINGLE



**10MAGLOCK6UL**  
600 LB, DOUBLE



**10MAGLOCK1UL**  
1200 LB, SINGLE



**10MAGLOCK5UL**  
1200 LB, DOUBLE



**10LZBRMAG3UL**  
L & Z BRACKET  
FOR 600 LB, SINGLE



**10LZBRMAG1UL**  
L & Z BRACKET  
FOR 1200 LB, SINGLE



**10MAG6LZUL**  
(2) L & Z BRACKET  
FOR 600 LB, DOUBLE



**10MAG5LZUL**  
(2) L & Z BRACKET  
FOR 1200 LB, DOUBLE



**10UBRACKETUL**  
GLASS DOOR  
MOUNTING KIT



**10FILLER14UL**  
0.25 × 1.25 INCH  
FILLER PLATE



**10FILLER12UL**  
0.50 × 1.25 INCH  
FILLER PLATE



**10FILLER34UL**  
0.75 × 1.25 INCH  
FILLER PLATE



**10FILLER58UL**  
0.0625 × 0.0625 INCH  
FILLER PLATE



**10RIMHOUSING3UL**  
ARMATURE PLATE  
HOUSING, 600 LB



**10RIMHOUSING1UL**  
ARMATURE PLATE  
HOUSING, 1200 LB



**10SPACER3UL**  
VERTICAL SPACER  
BRACKET, 600 LB



**10SPACER1UL**  
VERTICAL SPACER  
BRACKET, 1200 LB

