



EM-1200 Series Electromagnetic Locks

Applications, Features, Specifications, and Accessories

EM-1200 Series Maglock: 1200 lb. holding force electromagnetic lock recommended for exterior and perimeter doors where high security is required.



EM-1200-D



EM-1200

Features:

- HOLDING FORCE:** 1200 lb. holding force
- SUITABLE FOR:** 90° degree out-swinging doors
- POWER:** Low power consumption with high efficiency
- INDICATOR:** LED indicator and monitor output
- MOUNTING:** Surface mounts easily
- FINISH:** Attractive brushed stainless steel finish (US32D)
- MATERIALS:** Use of solid steel material allows strong holding force and no residual magnetism

1200 lb. Single Maglock
Part# **EM-1200**

L & Z Brackets
Part# **EM-BR1200**

1200 lb. Double Maglock
Part# **EM-1200-D**

U Bracket
Part# **EM-UB1200**

Circuit Board Only
Part# **EM-1200CBO**

Armature plate housing
Part# **EM-AP1200**

Specifications:

- POWER SUPPLY:** 12VDC or 24VDC
- CURRENT:** 500mA @ 12V or 250mA @ 24V
- FAIL TYPE:** Fail-Safe
- INDICATOR:** Built-in lock status LED's indication
 - LED indicator with bond sensor
 - Terminals to monitor bond included
 - Red = Power On
 - Green = Bond Sensor Activated
- EM-1200:** Single lock
- DIMENSIONS:** 10.43" (L) x 2.6" (W) x 1.6" (D)
- EM-1200-D:** Double lock
- DIMENSIONS:** 20.86" (L) x 2.6" (W) x 1.6" (D)

Accessories:



EM-BR1200: L and Z brackets for 1200lb. maglocks



EM-UB1200: U bracket glass holder for 1200lb. maglocks



EM-AP1200: Armature plate housing for 1200lb. maglocks

BLUEWAVE
security

The IP Lock and Security Company

2270 Camino Vida Roble
Carlsbad, CA 92011

Tel: 760-929-9596

Email: Sales@BlueWaveSecurity.com

Distributed by:

