STI METAL PROTECTIVE CABINETS

















PRODUCT OVERVIEW

These enclosures for electrical and electronic equipment (up to 1000V) provide personal protection from hazardous parts and provides a degree of protection to enclosed equipment. EM models are constructed for indoor use. All enclosures offer protection against vandalism either accidental or intentional. The size allows the enclosures to house significantly sized electronic devices with space to spare. Enclosures mount to the wall enabling units to be protected in their designated location.

They have a durable finish to help protect against corrosion.

KEY FEATURES

General Information

 Can be used in all wiring applications as a junction, splice or power supply cabinet

Design

- · Cost effective, low maintenance and compact design.
- · Continuous piano type hinge.

Construction

- Heavy-duty enclosures are constructed with a powder coated metal to help protect against corrosion.
- Metal thickness meets or exceeds
 Type 1 requirements.

Installation

• Enclosures mount to the wall enabling units to be protected in their designated location.

Options

 Thumb or key lock (option sold separately).

EM Models:

- Backplate (sold separately) may be mounted into cabinet.
- · Back design helps accommodate uneven walls or mounting surface.
- Top, side and bottom knockouts are 1/2" and 3/4".
- UL, cUL Listed, Type 1 (see approvals).

7560/7561 Models:

- · UL Listed, Type 4.
- · Includes backplate and two 1/4 turn latches.



STI Metal Protective Cabinets

Dimensions and Technical Information

MODELS AVAILABLE

STI-7560*Metal Protective Cabinet with windowSTI-7561*Metal Protective Cabinet without windowSTI-EM07123.5Metal Protective Cabinet 18 gaugeSTI-EM111103Metal Protective Cabinet 18 gaugeSTI-EM111504Metal Protective Cabinet 18 gaugeSTI-EM121204Metal Protective Cabinet 18 gaugeSTI-EM151804Metal Protective Cabinet 18 gaugeSTI-EM151804Metal Protective Cabinet 17 gauge

APPROVALS

· STI-7560 and STI-7561 UL Listed, Type 4 · EM models UL, cUL Listed, Type 1

Many polycarbonate cabinets also available.

*A/C or heat options available, also available without window

Part #	Н	W	D
STI-7560/STI-7561	36" (914mm)	24" (610mm)	8.79" (161mm)
STI-EM07123.5	12.20" (310mm)	7.73" (196mm)	3.84" (98mm)
STI-EM08073.5	8.40" (213mm)	7.66" (195mm)	3.80" (97mm)
STI-EM111103	11.20" (284mm)	11.28" (286mm)	3.30" (84mm)
STI-EM111504	15.20" (386mm)	11.28" (286mm)	4.30" (109mm)
STI-EM121204	12.20" (310mm)	12.7" (323mm)	4.30" (109mm)
STI-EM151804	18.20" (462mm)	15.28" (388mm)	4.30" (109mm)

ACCESSORIES FOR EM MODELS

KL544 Key lock TL644 Thumb lock

STI-MBP0506 14 gauge backplate for STI-EM07123.5 and STI-EM08073.5**
STI-MBP1010 14 gauge backplate for STI-EM111103 and STI-EM121204

STI-MBP0913 14 gauge backplate for STI-EM111504 **STI-MBP1316** 14 gauge backplate for STI-EM151804

KIT-H18019 Standoff Kit for MBPs, qty. 6

^{**}Includes a top or bottom plate mount option