

# FMC-420RW Single Action Call Points LSN improved

www.boschsecurity.com



**BOSCH**  
Invented for life




- ▶ Alarm triggering by pressing the black marking or breaking the glass pane
- ▶ Protection against injury through foil-labeled glass pane
- ▶ LED display for triggered alarm or inspection evaluation
- ▶ Individual call point identification
- ▶ Call point query routines with evaluation and multiple transmission

FMC-420RW Single Action Call Points are used for manual triggering and can be employed in both the Local SecurityNetwork (LSN) and the LSN improved version.

## Functions


### Single action call points with glass pane:



Pressing the black marking (1) breaks the glass pane (3), which triggers the alarm and causes the LED (2) to flash.

Single action call points can be reset with the test key and by replacing the glass pane (3). The LED display (2) goes dark.

### Resettable single action call points:



Pressing the black marking (1) triggers the alarm. The alarm status is indicated by the changed window color (4) and the flashing LED (2).

Single action call points can be reset using the test key. The LED (2) goes dark.

### Individual call point identification

Neither single action call points with glass pane nor resettable single action call points are reset on the fire panel.

Individual call point identification with display of the call point address on the fire panel ensures the quick location of the triggered call point.

### Certifications and approvals

Region	Certification	
Germany	VdS	G 207087 FMC-420RW
	VdS	G210017 FMC-420-RW-HSGRD/-HSRRD
Europe	CE	FMC-420RW-GSGBU/-GSRBU/-GSGYE/-GSRYE
	CE	FMC-420RW-GSGRD/-GSRRD/-GFGRD/-GFRRD
	CE	FMC-420RW-HSGRD/-HSRRD
	CPD	0786-CPD-20333 FMC-420RW
	CPD	0786-CPD-20942 FMC-420RW-HSGRD
	CPD	0786-CPD-20943 FMC-420RW-HSRRD
Ukraine	MOE	UA1.016.0091994-09 FMC-420RW

### Installation/configuration notes

- Manual call points must be mounted visibly along escape and rescue routes (e.g. exits, passageways, stairwells) and be easily accessible.
- An installation height of 1400 mm ±200 mm (55 in. ±8 in.), measured from the middle of the manual call point to the floor, must be maintained.
- Manual call points must be sufficiently lit with daylight or another light source (including emergency lighting if present).
- The maximum number of LSN elements that can be connected depends on their current consumption from the LSN data line. The limit values should be taken from the product information supplied with the fire panel used.
- Standards, guidelines and planning recommendations regarding the installation location etc. should also be taken into consideration.
- The regulations of the local fire services must be observed.

### Parts included

Quantity	Components
1	FMC-420RW-GSGRD Manual Call Point with Glass Pane, Surface-mounted, Red
1	FMC-420RW-GSRRD Manual Call Point Resettable, Surface-mounted, Red
1	FMC-420RW-GFGRD Manual Call Point with Glass Pane, Flush-mounted, Red
1	FMC-420RW-GFRRD Manual Call Point Resettable, Flush-mounted, Red
1	FMC-420RW-GSGYE Manual Call Point with Glass Pane, Surface-mounted, Yellow
1	FMC-420RW-GSRYE Manual Call Point Resettable, Surface-mounted, Yellow

- 1 FMC-420RW-GSGBU Manual Call Point with Glass Pane, Surface-mounted, Blue
- 1 FMC-420RW-GSRBU Manual Call Point Resettable, Surface-mounted, Blue
- 1 FMC-420RW-HSGRD Manual Call Point for Outdoor Use, with Glass Pane, Surface-mounted, Red/White
- 1 FMC-420RW-HSRRD Manual Call Point for Outdoor Use, Resettable, Surface-mounted, Red/White



#### Notice

The FMC-KEY-RW Test Key is not included in the delivery and must be ordered separately. For the flush-mounted variants, the bezel has to be ordered separately.

### Technical specifications

#### Electrical

Operating voltage	15 VDC to 33 VDC
Current consumption	0.4 mA

#### Mechanical components

Dimensions (H x W x D)	
• FMC-420RW-GFGRD, FMC-420RW-GFRRD	107 mm x 107 mm x 38.5 mm (4.2 in. X 4.2 in. X 1.5 in.)
• FMC-420RW-GSGRD, FMC-420RW-GSGBU, FMC-420RW-GSGYE	87 mm x 87 mm x 56 mm (3.4 in. X 3.4 in. X 2.2 in.)
• FMC-420RW-GSRRD, FMC-420RW-GSRBU, FMC-420RW-GSRYE	87 mm x 87 mm x 56 mm (3.4 in. X 3.4 in. X 2.2 in.)
• FMC-420RW-HSGRD, FMC-420RW-HSRRD	108 mm x 108 mm x 66 mm (4.25 in. X 4.25 in. X 2.6 in.)
Housing material	Plastic, ASA
Colors	
• Red	RAL 3001
• Blue	RAL 5005
• Yellow	RAL 1003
• Red/white	RAL 3001 / RAL 9003

#### Environmental conditions

Protection category according to EN 60529	IP 54
Protection category according to EN 60529 for FMC-420RW-HSGRD FMC-420RW-HSRRD	IP 67

Permissible operating temperature	-25 °C to +70 °C
Permissible rel. humidity	< 96 %

### Ordering information

#### **FMC-420RW-GSGRD Manual Call Point with Glass Pane, Red**

analog addressable manual call point with glass pane for indoor use, direct alarm triggering (type A), surface-mounted, red  
Order number **FMC-420RW-GSGRD**

#### **FMC-420RW-GSRRD Manual Call Point Resettable, Red**

resettable analog addressable manual call point for indoor use, direct alarm triggering (type A), surface-mounted, red  
Order number **FMC-420RW-GSRRD**

#### **FMC-420RW-GFGRD Manual Call Point with Glass Pane, Flush-mounted, Red**

analog addressable manual call point with glass pane for indoor use, direct alarm triggering (type A), flush-mounted, red  
Order number **FMC-420RW-GFGRD**

#### **FMC-420RW-GFRRD Manual Call Point Resettable, Flush-mounted, Red**

resettable analog addressable manual call point for indoor use, direct alarm triggering (type A), flush-mounted, red  
Order number **FMC-420RW-GFRRD**

#### **FMC-420RW-GSGYE Manual Call Point with Glass Pane, Yellow**

analog addressable manual call point with glass pane for indoor use, direct alarm triggering (type A), surface-mounted, yellow  
Order number **FMC-420RW-GSGYE**

#### **FMC-420RW-GSRYE Manual Call Point Resettable, Yellow**

resettable analog addressable manual call point for indoor use, direct alarm triggering (type A), surface-mounted, yellow  
Order number **FMC-420RW-GSRYE**

#### **FMC-420RW-GSGBU Manual Call Point with Glass Pane, Blue**

analog addressable manual call point with glass pane for indoor use, direct alarm triggering (type A), surface-mounted, blue  
Order number **FMC-420RW-GSGBU**

#### **FMC-420RW-GSRBU Manual Call Point Resettable, Blue**

resettable analog addressable manual call point for indoor use, direct alarm triggering (type A), surface-mounted, blue  
Order number **FMC-420RW-GSRBU**

#### **FMC-420RW-HSGRD Manual Call Point with Glass Pane, Red/White, Outdoor**

analog addressable manual call point with glass pane for outdoor use, direct alarm triggering (type A), surface-mounted, red/ white  
Order number **FMC-420RW-HSGRD**

#### **FMC-420RW-HSRRD Manual Call Point Resettable, Red/White, Outdoor**

resettable analog addressable manual call point for outdoor use, direct alarm triggering (type A), surface-mounted, red/ white  
Order number **FMC-420RW-HSRRD**

#### **Accessories**

##### **FMC-BEZEL-RD Bezel for MCP RW, red**

Frame for the flush-mounted variant of the RW call points.  
1 unit = 4 bezels  
Order number **FMC-BEZEL-RD**

##### **FMC-BEZEL-WH Bezel for MCP RW, white**

Frame for the flush-mounted variant of the RW call points.  
1 unit = 4 bezels  
Order number **FMC-BEZEL-WH**

##### **FMC-SEAL-RW**

Seal for clear hinged flap  
1 unit = 100 seals  
Order number **FMC-SEAL-RW**

##### **FMC-SPACER-RWRD Spacer, Red**

For the flush-mounted variant of the RW call points. Its use increases the storage room for the cables.  
1 unit = 5 spacers  
Order number **FMC-SPACER-RWRD**

##### **FMC-SPGL-RW Spare Glasses**

Spare glasses for all RW call points.  
1 unit = 5 spare glasses  
Order number **FMC-SPGL-RW**

##### **FMC-SIGN-RW Out of Order Sign**

Used instead of the glass pane when a call point is not ready for use.  
1 unit = 5 signs  
Order number **FMC-SIGN-RW**





##### **FMC-KEY-RW Test Key**





The key can open, check, and reset manual call points.  
1 unit = 1 key  
Order number **FMC-KEY-RW**

##### **FMC-FLAP-RW Clear Hinged Flap**

To protect against accidental triggering; with seal.  
1 unit = 5 flaps  
Order number **FMC-FLAP-RW**

**FMC-420RW Single Action Call Points LSN improved version**

	<b>FMC-420RW-GSGRD Manual Call Point with Glass Pane, Red</b>	<b>FMC-420RW-GSRRD Manual Call Point Resettable, Red</b>	<b>FMC-420RW-GFGRD Manual Call Point with Glass Pane, Flush- mounted, Red</b>	<b>FMC-420RW-GFRRD Manual Call Point Resettable, Flush- mounted, Red</b>
				
Design	with glass pane	resettable	with glass pane	resettable
Range of use	indoor	indoor	indoor	indoor
Mounting	surface-mounted	surface-mounted	flush-mounted	flush-mounted
Operating voltage	15 V DC to 33 V DC	15 V DC to 33 V DC	15 V DC to 33 V DC	15 V DC to 33 V DC
Current consumption	0.4 mA	0.4 mA	0.4 mA	0.4 mA
Protection category	IP 54	IP 54	IP 54	IP 54
Permissible operating temperature	-25°C to +70°C	-25°C to +70°C	-25°C to +70°C	-25°C to +70°C
Color	red, RAL 3001	red, RAL 3001	red, RAL 3001	red, RAL 3001

	<b>FMC-420RW-GSGYE Manual Call Point with Glass Pane, Yellow</b>	<b>FMC-420RW-GSRYE Manual Call Point Resettable, Yellow</b>	<b>FMC-420RW-GSGBU Manual Call Point with Glass Pane, Blue</b>	<b>FMC-420RW-GSRBU Manual Call Point Resettable, Blue</b>
				
Design	with glass pane	resettable	with glass pane	resettable
Range of use	indoor	indoor	indoor	indoor
Mounting	surface-mounted	surface-mounted	surface-mounted	surface-mounted
Operating voltage	15 V DC to 33 V DC	15 V DC to 33 V DC	15 V DC to 33 V DC	15 V DC to 33 V DC
Current consumption	0.4 mA	0.4 mA	0.4 mA	0.4 mA
Protection category	IP 54	IP 54	IP 54	IP 54
Permissible operating temperature	-25°C to +70°C	-25°C to +70°C	-25°C to +70°C	-25°C to +70°C
Color	yellow, RAL 1003	yellow, RAL 1003	blue, RAL 5005	blue, RAL 5005

	<b>FMC-420RW-HSGRD Manual Call Point with Glass Pane, Red/White, Outdoor</b>	<b>FMC-420RW-HSRRD Manual Call Point Resettable, Red/White, Outdoor</b>
		
Design	with glass pane	resettable

	<b>FMC-420RW-HSGRD Manual Call Point with Glass Pane, Red/White, Outdoor</b>	<b>FMC-420RW-HSRRD Manual Call Point Resettable, Red/White, Outdoor</b>
Range of use	outdoor	outdoor
Mounting	surface-mounted	surface-mounted
Operating voltage	15 V DC to 33 V DC	15 V DC to 33 V DC
Current consumption	0.4 mA	0.4 mA
Protection category	IP 67	IP 67
Permissible operating temperature	-25°C to +70°C	-25°C to +70°C
Color	red/white, RAL 3001/9003	red/white, RAL 3001/9003

**Represented by:****North America:**

Bosch Security Systems, Inc.  
130 Perinton Parkway  
Fairport, New York, 14450, USA  
Phone: +1 800 289 0096  
Fax: +1 585 223 9180  
security.sales@us.bosch.com  
www.boschsecurity.us

**Europe, Middle East, Africa:**

Bosch Security Systems B.V.  
P.O. Box 80002  
5617 BA Eindhoven, The Netherlands  
Phone: + 31 40 2577 284  
Fax: +31 40 2577 330  
emea.securitysystems@bosch.com  
www.boschsecurity.com

**Asia-Pacific:**

Robert Bosch (SEA) Pte Ltd, Security Systems  
11 Bishan Street 21  
Singapore 573943  
Phone: +65 6571 2808  
Fax: +65 6571 2699  
apr.securitysystems@bosch.com  
www.boschsecurity.asia

**China:**

Bosch (Shanghai) Security Systems Ltd.  
203 Building, No. 333 Fuquan Road  
North IBP  
Changning District, Shanghai  
200335 China  
Phone +86 21 22181111  
Fax: +86 21 22182398  
www.boschsecurity.com.cn

**Latin America and Caribbean:**

Robert Bosch Ltda Security Systems Division  
Via Anhanguera, Km 98  
CEP 13065-900  
Campinas, Sao Paulo, Brazil  
Phone: +55 19 2103 2860  
Fax: +55 19 2103 2862  
latam.boschsecurity@bosch.com  
www.boschsecurity.com