

1U 19in Steel Vertical Wall Mount Equipment Rack Bracket

Product ID: RK119WALLV



The RK119WALLV 1U 19in Steel Vertical Wall Mount Equipment Rack Bracket offers a versatile storage solution allowing rackmount equipment (Network devices, power strips, patch panels) to be mounted vertically (flush with wall) to save space. Alternatively, the 1U bracket can be installed horizontally under a desk, making it easy to access installed equipment directly from your workspace. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Perfect for SoHo (small office, home office) environments, the wallmount bracket features a sturdy steel design constructed to EIA-310 19in rack standards, and offers space-savings for environments lacking the footprint space for a full size server equipment rack. Suitable for mounting on virtually any wall/ceiling surface (e.g. drywall), the bracket mounting holes are positioned at exactly 16in apart, matching standard construction framework.

Backed by a StarTech.com Lifetime Warranty.

Need more storage space? StarTech.com also offers a [2U 19in Wallmount Bracket](#), a [3U 19in Wallmount Bracket](#) and a [4U 19in Wallmount Bracket](#).

Certifications, Reports and Compatibility



Applications

- Mount networking and telecommunication equipment flush against the wall
- Mount KVM switches or workstations under a desk or work bench to free up work space
- Ideal for small and medium businesses needing rack solutions

Features

- Constructed to meet EIA-310 19" rack standards
- Compatible with most 19" rack mountable equipment
- TAA compliant for GSA Schedule purchases
- Equipment can be vertically wall mounted, or horizontally under a desk
- Wall mounting holes are 16" center to center for greater stability, and mounting into standard wall studs
- Arrives fully assembled with cage screws and nuts for mounting equipment
- Made from solid steel for durability

Hardware	Warranty	Lifetime
	Additional Required Tools	Phillips Screwdriver
	Adjustable Mounting Rails	No
	Cable Management	No
	Casters	No
	Fan(s)	No
	Frame Type	Open Frame
	Front Door Construction	Open
	Industry Standards	EIA-310-D EIA RS310-C
	Ladder Type	L-Shape
	Mounting Holes	Square
	Number and Type of Included Cage Nuts	4 - M5
	Rack Type	2-Post
	Tools Included	No
	U Height	1U
	U Markings	No
	Wallmountable	Yes
Performance	Weight Capacity (Stationary)	125.3 lb [56.7 kg]
Special Notes / Requirements	Note	Package includes 1 ½" screws for mounting to wood surfaces, additional hardware will be required for other materials
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	External Depth	5.9 in [150 mm]
	External Height	2.3 in [59 mm]
	External Width	19.8 in [503 mm]
	Internal Width	19.6 in [498 mm]
	Product Height	2.3 in [59 mm]
	Product Length	5.9 in [150 mm]
	Product Weight	23.3 oz [660 g]

	Product Width	19.8 in [503 mm]
	Rail Thickness	0.1 in [2 mm]
Packaging Information	Flat Pack (Assembly Required)	No
	Shipping (Package) Weight	2 lb [0.9 kg]
What's in the Box	Included in Package	1 - Vertical Wall Mount Bracket
		4 - Cage nuts and screws (4 Each)
		6 - Self Tapping Wood Screws - 3/16" x 1 1/2"

Product appearance and specifications are subject to change without notice.