



BMP®61

LABEL PRINTER

Smarter, Better, Faster, Stronger

Brady's BMP®61 label printer is designed for quick and efficient identification of wires, cables and components.

With high performance materials that can handle the toughest industrial identification applications, this printer is your rugged and reliable partner in the field and dependable workhorse in the shop. It features multiple user interfaces, touch screen capabilities and a variety of ways to connect, manage and save your data.

With the BMP®61 printer in hand, you're ready to tackle identification tasks- and finish those tasks flawlessly.

KEY FEATURES

The BMP®61 printer is designed to be simple, efficient, versatile and reliable with the following features:

- Large, colour touch screen display
- Data connectivity with USB 2.0 ports, flash drive support & WiFi
- Wide cover opening & large material bay offers easy material loading
- Smart cell technology for quick, automatic label formatting
- Simple user interface and intuitive QWERTY style key pad
- Die-cut, continuous and custom label supplies up to 51mm for a range of applications
- Tested to survive a 1.2m drop with rubber bumpers and durable design
- Utility strap for improved storage and handling
- 300 dpi print head for clear, crisp font

PRINTER CATALOGUE NUMBERS

Part No:	Reference #	Description
877863	BMP61-W	BMP61 Label Printer with WiFi
Printer Accessories		
146220	BMP-HC-1	Hardcase Accessory
146233	BMP-STRAP-1	Carrying Strap
146221	BMP-MAGNET-1	Magnet Accessory
133260	BMP41-QC	External Battery Quick Charger
133255	BMP41-BATT	Rechargeable NiMH Battery
146228	BMP61-BATCOV	Battery Cover
146222	BMP61-CUTTER	Cutter Accessory
18556	PCK-5	Cleaning Kit 5-Pack

KEY SPECIFICATIONS

Printer	
Includes	Printer ships with AC adapter/battery charger, NiMH rechargeable battery, USB cord, utility strap, hardcase, PTL-19-423 label material, M61-R6010 ribbon, Quick Start Guide and Driver Disks
Weight	1.45 kg (equipped with supplied media & ribbon)
Size	328 (L) x 107 (W) x 106 (H) mm
Keyboard Type*	QWERTY, AZERTY, QWERTZ, CYRILLIC
Min. Label Width	6.4 mm
Max. Label Width	50.8 mm
Internal Memory Capacity	512MB of RAM/ 256MB Flash
Materials Supported	
Materials Supported	600+ standard parts: continuous tapes, die cut and bulk label rolls, custom made labels and tapes
Fonts/Graphics/Symbolologies	
Bar Code Type	Code 39 and 128, other via software
Text Sizes (pt)	4 to 174pt + auto-sizing
Built-In Fonts	Brady Alpine, Brady Fixed Width
Software & Connectivity	
Connectivity Options	USB 2.0, USB Flash Drive, WiFi
Software Compatibility	Brady Workstation, Labelmark 6.0, Brady Mobile Apps
Power Supply	
Battery Type	Rechargeable NiMH Battery
Power Supply	AC Power
Compliance	
Approval/Compliance	FCC Class A, UL-BMP61 WLAN 1EEE 802.11 b/g/n-BMP61-W

PRINTER RIBBONS

All materials in the printer will work with a new series of M61 ribbons that easily fit into the printer.

Part No:	Reference #	Colour	Description	Size
148134	M61-R6610	Black	R6600 Series Ribbon	50.8 mm x 22.85 m
148128	M61-R6010	Black	R6000 Series Ribbon	50.8 mm x 22.85 m
148135	M61-R6410	Black	R6410 Series Ribbon	50.8 mm x 22.85 m
148129	M61-R4310	Black	R4300 Series Ribbon	50.8 mm x 22.85 m
148130	M61-R6210	Black	R6200 Series Ribbon	50.8 mm x 22.85 m
148131	M61-R4410-WT	White	R4400 Series Ribbon	50.8 mm x 22.85 m
148136	M61-R6810-WT	White	R6800 Series Ribbon	50.8 mm x 22.85 m
148086	M61-R6710-WT	White	R6710 Series Ribbon	50.8 mm x 22.85 m
148132	M61-R4410-RD	Red	R4400 Series Ribbon	50.8 mm x 22.85 m
148133	M61-R4410-BL	Blue	R4400 Series Ribbon	50.8 mm x 22.85 m



*Available in select countries. Specifications subject to change without notice.
© 2017 Brady Worldwide Inc. All Rights Reserved.