
# AO19 SERIES® AO19-1

## Low Energy Automatic Door Operators for Single Doors

The AO19 Series Automatic Operator for single doors is an easy to install, heavy duty product for high use and high abuse low energy applications. The AO19 Series meets requirements for ANSI/BHMA A156.19 (American National Standard for Power Assist and Low Energy Power Operated Doors) and provides standard features that meet the requirements of the American Disabilities Act.



Benefits		
Economical operator provides safe and easy access in	<ul> <li>Hanger plate allows quick installation</li> </ul>	<ul> <li>Reduced service calls due to heavy-duty construction</li> </ul>
medium to high-traffic and security areas	<ul> <li>Self-contained unit in an extruded case allows easy access for</li> </ul>	<ul> <li>3-way low-voltage ON/OFF/HOLD switch for ease of service and</li> </ul>
<ul> <li>Provides ADA compliant access to handicap applications</li> </ul>	maintenance and adjustments	setup
Quiet operation	<ul> <li>Works with existing access control, locking and computer signal devices</li> </ul>	<ul> <li>115VAC power plug-in mounted in header</li> </ul>
		<ul> <li>Easy manual use</li> </ul>
Features		
• Available in single, pair (twin) for independent, simultaneous and dual egress openings	<ul> <li>Adjustable delayed activation for sequenced vestibule doors</li> </ul>	<ul> <li>Push &amp; Go (Use for Handicap) activates when door is manually pushed to open. Must be selected</li> </ul>
	<ul> <li>Reverse on obstruction stalls a door during closing cycle and</li> </ul>	to activate.
<ul> <li>Power close applies a reverse power to aid in latch check position. Must be selected to activate.</li> </ul>	re-activates to open if an obstruction is sensed anytime before the latch position. Must be	<ul> <li>Electric lock relay provides an adjustable delay before door opens to unlock an electric strike, maglock</li> </ul>
<ul> <li>Single voltage source required to operate</li> </ul>	selected to activate.	or other types of electric locks - prevents binding
operate	<ul> <li>Adjustable closing speed</li> </ul>	
Mechanical Options		
LH Push - Left Hand Push	• 39.5" - Fits above most 36" doors	
RH Push - Right Hand Push	• 45.5" - Fits above most 42" doors	Where Trust is Built
• LH Pull - Left Hand Pull	• 52" - Fits above most 48" doors	<b>DTEX</b> <sup>®</sup>
RH Pull - Right Hand Pull		Life Safety and Security Door Hardware

### Accessories

• 104792 - Wireless Button Package (includes 2 push plates, 2 mounting boxes and 1 receiver)

Call for available activation options

### **Technical Information**

• PB-2048-3 - Mushroom switch, hard-wired

• DS-3681-630 - Electric Strike, cylindrical

> FAX (800) 653-3839 http://www.detex.com USA Sales: marketing@detex.com International Sales:

export@detex.com

Technical Information		
Power Requirements - • 115VAC 60 HZ 3 amps Motor	Module - • Activation input terminals • Form C lock switch terminals	<ul> <li>Push reveal depth up to 11" with standard arm. Extended arm available.</li> </ul>
<ul> <li>115VDC rectified</li> <li>1/8 hp</li> <li>60:1 gearbox</li> </ul>	<ul> <li>Safety lock-out built in</li> <li>17 additional features standard on board</li> </ul>	Pull reveal depth up to 5"
C C	Enclosure -	Listings and Approvals
	<ul> <li>7" h x 4 1/2" d</li> <li>Approximately 50 lbs</li> <li>Aluminum extrusion</li> </ul>	Certified to ANSI/UL 325 Tested - ANSI 156.19
Finishes		Meets ADA requirements
AL - 204-Ri Clear: Arch. Class II anodized coating, AA-M12C22A31	<ul> <li>BZ - 313-Ri Dark Bronze: Arch. Class II Anodized coating, AA-M12C22A32</li> </ul>	(5)
		3-Hour Fire Listed
Riser Diagram	Handing Diagram	Intertek
	LH Push RH Push	
AO19-1 RH Push	A019-1 LH Pull Exterior A019-1 Interior A019-1 A019-1 Interior A019-1 Interior A019-1 Interior A019-1 Interior A019-1 Interior	Detex Limited Warranty 3 Year Mechanical / 1 year Electrical Limited Manufacturer's Warranty
Shown with 10 Series Electric Latch Retraction (ER)	J J-box (sold separately) Detex flexible conduit with connections (optional)	Where Trust is Built EXAMPLE TO A CONTRACT OF THE SAFETY AND SECURITY DOOR Hardware Detex Corporation 302 Detex Drive New Braunfels, Texas 78130-3045 USA PH. (830) 629-2900
		(800) 729-3839

**Typical Application** 

#### August 27, 2015