



## LED-709HD

This versatile, high-definition, LED-backlit monitor is designed primarily for field testing, video production and remote surveillance applications. Multiple mounting options and battery pack options are available.

### Benefits

- LED backlight: brighter picture using less power
- Displays HD signals (1080i/p and 720p)
- 16:9 native aspect ratio
- Built-in 5-wire resistive touch screen
- Battery pack option available for mobility
- IR remote control

### Related Products

- LED-709KIT: monitor, tote bag and BP-563C rechargeable battery
- LED-709HDM: 7" LCD monitor w/ metal case
- LED-709HDML: flush mount w/ metal case
- LED-709HD2: rack mount w/ metal case

Specifications	
Mount	VESA 75 x 75mm; Removable Deskstand
HD Compatible	Yes
Anti Glare Coating	Yes
Case	Durable ABS Plastic
IR Remote Control	Yes
Native Aspect Ratio	16:9
Visible Screen Size (WH)	6" x 3.4" / 154.08 x 85.92mm
Resolution	800 x 480
Brightness Rating	250 cd/m <sup>2</sup> (Nit)
Contrast Ratio	500:1
Back Light	LED (20K)
Dot Pitch	0.0642(H) x 0.1790(V) mm
Number of Pixels	1.2M
Response Time	25ms (Rising/Falling)
Viewing Angle (L/R/T/B)	70/70/50/70 degrees
Dimensions	6.9" x 5.3" x 1.4" / 174 x 134 x 35mm
Operating Temp	-4 ~ 158°F / -20 ~ 70°C
Humidity	90%
Power Requirements	10 VDC to 27 VDC Input; 2A + pin; Negative Ground
Power Consumption	24 Watts (Max)
Touchscreen	x1 USB Output; 5-wire resistive
Composite	x1 RCA and x1 BNC Inputs on cable
VGA	x1 15-pin D-sub Input
HDMI	x1 Input
Audio / Speakers	x2 Speakers; x1 RCA Input on cable
Power	x1 2.1mm DC Input
Weight	Net: 0.75 lbs / 0.34 kg; Gross: 2.85 lbs / 1.3 kg

Specifications subject to change.