

1700A

"A" Grip

**1700B**

"B" Grip

**1700C**

"C" Grip

**2000C**

"C" Grip



1. All Trims are furnished with wrought plates and extruded or cast solid grips.
2. Specify Grip Design (A,B,C) ("A" Grip furnished standard for 1700 Series Trim, "C" Grip furnished standard for 2000 Series Trim)
3. 630 Trim is furnished for 628 Devices.
4. 626 Trim is furnished for 626W Devices.

Retrofit Applications

The R1700 Series Trim is designed to retrofit into other manufacturers' installations when used with the wide stile Apex Series Devices.

Consult factory for details.

4900A

"A" Lever

**4900B**

"B" Lever

**4900C**

"C" Lever

**4900D**

"D" Lever

**4900K**

"K" Knob

**V4908A****Vandal Resistant Trim**

A heavy duty lever trim designed to withstand abuse and vandalism. Composed of extra strength shock-absorbing "overload" springs and heavy duty investment cast stainless steel internal components. Lever returns to the "home" position eliminating the need to reset the lever.

Retrofit Applications

The R4900 Series Trim is designed to retrofit into other manufacturers' installations when used with the wide stile Apex Series Devices.

Consult factory for details.

1. All the escutcheons and levers are castings or forgings.
2. Specify Lever or Knob Design (A,B,C,D,K) and Handing ("A" Lever x RHRB furnished standard)
3. 626 Trim furnished for 626W, 628 and 630 Devices.
 - For Trim dimensions see page 38.
 - Trims are BHMA certified for ANSI 156.3, Grade 1.
 - Trims are through bolted and will cover 161 and 86 cutouts (except for 2000C Trim).
 - Cylinder, Rim Type, not furnished standard. For cylinder details see page 19.

ANSI Function	01	02	03	05	08	10*	14	15
	Exit Only (cover plate)	Dummy Trim	Key Retracts Latchbolt	Key Locks/Unlocks Thumbpiece	Key Locks/Unlocks Lever/Knob	Double Cylinder Inside Key Locks/Unlocks Lever/Knob	No Cylinder Lever/Knob Always Active	No Cylinder Thumbpiece Always Active
Device Nos.	2101 FL2101	2102	2103** FL2103**	2105 FL2105	2108 FL2108	2110 FL2110	2114 FL2114	2115 FL2115
Trim Nos.	1701 R1701 2001 4901 R4901	1702A R1702A 2002C 4902A R4902A	1703A R1703A 2003C 4903A R4903A	1705A R1705A 2005C	4908A V4908A R4908A RV4908A	4908A V4908A R4908A RV4908A	4914A R4914A	1715A R1715A 2015C

Device with Trim:

Device No. _____

Add **Prefix** for options,
see page 4.Add **Suffix**: for options, see page 4.Add **Prefix**: "V" Vandal Resistant Lever Trim
"R" Retrofit TrimAdd **Suffix**: Lever or Knob Design (A,B,C,D, K)
Grip Design (A,B,C)Add **Suffix**: "KNR" Knurled Lever or Grip**TS2108CD x V4908AKNR x RHRB x 630 x S300 x 3'-0" x 7'-0" x 1-3/4"**

Device w/options

Trim No.

Hand

Finish

Strike

Door Size

Device Only: Device no., hand, finish, strike, and door size including thickness:
(e.g. TS2108CD x RHRB x 630 x S300 x 3'-0" x 7'-0" x 1-3/4")

Trim Only: Trim no., hand, finish, strike, and door size including thickness: (e.g. V4908A x RHRB x 626 x 1-3/4")

* "10" Function is handed

** 2103 & FL2103 x Cylinder Only Application includes Cylinder Attachment Kit "CA-03"

WIRELESS ACCESS MANAGEMENT SYSTEM (continued)

B) BEST® EXQ Trim

The BEST® EXQ Trim provides battery powered online lock/unlock capability for applications utilizing exit device hardware. Used in conjunction with the STANLEY® WQX-PG Portal Gateway and Software, the EXQ trim can receive a wireless command for Lock/Unlock activation. In doing so, the respective facility has immediate efficient pull-side access control for openings that utilize exit device hardware. The EXQ comes standard with a (DS) Door Position Switch. In addition, the trim is equipped with lead wires to integrate the Q2000 Touchbar and Latchbolt Monitoring switches.

The BEST EXQ trim is offered with four different activation styles to choose from. These four types are listed below.

1. **MS** – Magnetic Stripe
2. **DV** – Dual Validation (Magnetic Stripe + Keypad)
3. **PH** – HID Proximity
4. **PM** – Indala Proximity

EXQ Trim Features

- Handing (Field reversible)

EXQ Trim Specifications

Materials – Internal parts are brass, zinc, or corrosion treated steel.

Escutcheons – 11.7" H x 3.4" W x 1.2" D.

Door thickness – Standard lock configuration designed for doors 1 3/4" (44mm) – 2 1/4" (57mm) thick.

Lever handle – Brass, bronze, or stainless steel base material. Lever styles 14 and 15 return to a minimum of 1/2" (12mm) of door surface.

Finishes – **606** – satin brass, clear coated,

613* – oxidized satin bronze, oil rubbed,

626 – satin chromium plated (brass base material),

690** – dark bronze coated (brass base material)

* 613 finish is designed to wear over time, providing an "antique" appearance.

** 690 finish will continue as a dark brown appearance over time.



**A) Precision™
Q2103 Exit Device**

**B) BEST®
EXQ Trim**

EXQ Trim Exit Device Compatibility

Apex 2000 Series Wide Style Exit Devices:


- Rim device – **2103**
- Surface vertical rod – **2203**
- Concealed vertical rod – **2703**
- Mortise – **2303**

Note: includes key-override

EXQ Trim Reader Styles



EXQ – Function

With key override	Latchbolt operated by:
	<ul style="list-style-type: none"> • Outside key • Outside lever-unless locked by internal motor drive mechanism • Touchbar
	Outside lever locked by:
	<ul style="list-style-type: none"> • Internal motor drive mechanism operated by time-activated electronic signal
	Outside lever unlocked by:
	<ul style="list-style-type: none"> • Internal motor drive mechanism operated by time-activated electronic signal or by valid card/PIN
	Inside hardware is always unlocked

For more information on other trims or trim readers refer to: BEST® EZ series, NT500, B.A.S.I.S. G, B.A.S.I.S. V, and Wireless Access Management catalogs.

Wireless Access Management System continued on pages 30 and 32