

## iCLASS + Prox card - 202 / 212

iCLASS + Prox cards can be ordered either with both SIO and iCLASS programming or iCLASS programming only.

Ensure each required option has been checked with the appropriate choice to fulfill a completed order form.

Base Model  202 Standard PVC  212 Composite 40% Polyester / PVC\*

### iCLASS Memory Size and Allocation (Select one option)

- 0 - 2k Bits (256 Bytes) with 2 Application Areas
- 3 - 32k Bits (4K Bytes) Application areas 16k/2+16k/1
- 4 - 32k Bits (4K Bytes) Application areas 16k/16+16k/1

### Programming (Select one option)

- HP - Programmed with Security Identity Object (SIO), and standard iCLASS Access control application, 125KHz Unprogrammed.<sup>1</sup>
- HB - Programmed with Security Identity Object (SIO), and standard iCLASS Access control application, programmed, Specify Programming Information<sup>1</sup>
- P - Programmed with standard iCLASS Access Control Application, 125 KHz Unprogrammed.
- B - Programmed 125 kHz Proximity and iCLASS. Specify Programming Information.
- C - iCLASS Unprogrammed, for use with iCLASS SE Encoder, Prox technology blank.
- A - iCLASS Unprogrammed, for use with iCLASS SE Encoder, Prox technology programmed. Specify Programming Information.
- K - iCLASS Programmed, HITAG1 blank. Specify Programming Information.
- M - iCLASS Programmed, HITAG2 blank. Specify Programming Information.
- R - iCLASS configured field programmable, HITAG1 blank.
- I - iCLASS configured field programmable, HITAG2 blank.

### Front Packaging (Select one option)

- G - Plain White with Gloss Finish
- C - Custom Artwork with Gloss Finish - Specify Custom Artwork Number<sup>2</sup>

### Back Packaging (Select one option)

- G - Plain White with Gloss Finish<sup>3</sup>
- C - Custom Artwork with Gloss Finish - Specify Custom Artwork Number<sup>2</sup>
- 1 - Plain White with Gloss Finish with Magnetic Stripe<sup>3</sup>
- 3 - Custom Artwork with Gloss Finish with Magnetic Stripe - Specify Custom Artwork Number<sup>2</sup>

### iCLASS Card Numbering<sup>4</sup> (Select one option)

- M - Sequential Matching Encoded/Printed (Inkjetted)<sup>7</sup>
- N - No Printed Card Numbering
- S - Sequential Encoded/Sequential Non-Matching Printed (Inkjetted)<sup>7</sup>
- R - Random Encoded/Non-Matching Sequential Printed (Inkjetted)<sup>7</sup>
- A - Sequential Matching Encoded/Printed (Laser Engraved)<sup>5</sup>
- B - Sequential Encoded/Sequential Non-Matching Printed (Laser Engraved)<sup>5</sup>
- C - Random Encoded/Non-Matching Sequential Printed (Laser Engraved)<sup>5</sup>

### Slot Punch<sup>6</sup> (Select one option)

- V - Vertical Slot Punch
- N - No slot punch, This card can be slotted vertically, Printed Vertical Slot Indicators

### 125 kHz Card Numbering<sup>4</sup> (Select one option)

- M - Sequential Matching Encoded/Printed (Inkjetted)<sup>7</sup>
- N - No Printed Card Numbering
- S - Sequential Encoded/Sequential Non-Matching Printed (Inkjetted)<sup>7</sup>
- R - Random Encoded/Non-Matching Sequential Printed (Inkjetted)<sup>7</sup>
- A - Sequential Matching Encoded/Printed (Laser Engraved)<sup>5</sup>
- B - Sequential Encoded/Sequential Non-Matching Printed (Laser Engraved)<sup>5</sup>
- C - Random Encoded/Non-Matching Sequential Printed (Laser Engraved)<sup>5</sup>

### Option - Custom Artwork<sup>2</sup>

\_\_\_\_\_ (Specify Artwork Number - Refer to the Custom Artwork Forms for new artwork)

Enter your final card options from the above selections. Example: 2020HPGGNNN

Final Part Number										-	(Options #)
-------------------	--	--	--	--	--	--	--	--	--	---	-------------

