

# GV-VS2400 4CH H.264 TVI 1080p Video Server



- H.264
- 4-channel TVI 1080p / 720p and analog 960H / D1 real-time video
- 12V DC
- Tampering Alarm
- USB HDD Storage
- UMTS / 3G / 3.5G / 4G
- Automatic switch between WiFi and 3G
- Supports over 50 PTZ models
- 29 languages on web interface
- HD-TVI 1.0 / 2.0 standard
- ONVIF (Profile S) conformant

GV-VS2400 is a powerful H.264 Video Server with compact size and supports multiple applications. It supports 4-channel TVI 1080p / 720p and analog 960H / D1 real-time video, fully integrated with GV-System (GV-DVR/NVR) / GV-VMS to form the most powerful IP solution. GV-VS2400 converts analog signals into high resolution digitized images up to 2 megapixels. It also supports over 50 PTZ models to fulfill various project demands. It can record video to a local USB storage, forming the smallest video recorder. It can also activate Tampering Alarm alerts when cameras are tampered with, which can prevent criminal activities successfully.

#### **Specifications**

Video			
Video Standard			NTSC, PAL
Video Input			4 channels
Compression			H.264
Frame Rate	NTSC		30 fps per channel; 120 fps in total for 4 channels
	PAL		25 fps per channel; 100 fps in total for 4 channels
Resolution	NTSC	Main Stream	1920 x 1080 (Default) 1280 x 720, 640 x 360, 448 x 252 for TVI Signal
	HD	Sub Stream	640 x 360, 448 x 252 (Default) for TVI Signal
	NTSC	Main Stream	960 x 480, 720 x 480 (Default), 480 x 240, 360 x 240 for Analog Signal
	SD	Sub Stream	480 x 240, 360 x 240 (Default) for Analog Signal
	PAL	Main Stream	1920 x 1080 (Default) , 1280 x 720, 640 x 360, 448 x 252 for TVI Signal
	HD	Sub Stream	640 x 360, 448 x 252 (Default) for TVI Signal
	PAL	Main Stream	960 x 576, 720 x 576 (Default), 480 x 288, 360 x 288 for Analog Signal
	SD	Sub Stream	480 x 288, 360 x 288 (Default) for Analog Signal
Video Streaming			Configurable frame rate and bandwidth, Constant and variable bitrate
Video Adjustment			Brightness, Contrast, Saturation, Hue, Sharpness
Dual Streams			Yes
0 11011	Recomn	nended Type	5C-FB or above
Coaxial Cable	Maximu	m Length	300 m (984 ft)
Audio			
Audio Input			1 channel
Compression			G.711
Audio Support			Two-way

-1-GV-VS2400 June 27, 2017



Trigger	Schedule, Sensor Input, Motion Detection
	Store Video (AVI format)
	Send e-mails with captured images
Action	Upload captured images to FTP Server
	<ul> <li>Monitor through Center V2 and Vital Sign Monitor</li> </ul>
	<ul> <li>Activate relay outputs to control external devices</li> </ul>
	Remote upgrade by HTTP,
	Firmware upgrade utility included in the Software DVD
	USB HDD Storage
	Microsoft Internet Explorer 8.x or later
	IP address filtering
	Bulgarian / Czech / Danish / Dutch / English / French / German / Greek / Hebrew / Hindi / Hungarian / Italian / Indonesian / Japanese / Norwegian / Lithuanian / Persian / Polish / Portuguese / Romanian / Russian / Serbian / Simplified Chinese / Slovakian / Slovenian / Spanish / Thai / Traditional Chinese / Turkish
	/ Turnion
	10/100/1000 Base-T Ethernet,
	802.11b/g/n Wireless LAN (optional),
	Mobile broadband: UMTS, EDGE, etc. (optional)
	DHCP, DynDNS, FTP, HTTP, HTTPS, 3GPP/ISMA, NTP, ONVIF (Profile S), QoS
	(DSCP), RTSP, SMTP, SNMP, TCP, UDP, UPnP
	4 BNC ports
	1 port stereo phone jack, 3.5 mm/0.14"
	1 port stereo phone jack, 3.5 mm/0.14"
	4 inputs
	4 outputs
	RS-485 +/-
	RJ-45, 10/100/1000 Mbps
	2 ports (USB 2.0)
Input	12V, 3.0 A
Output	12V, 1.6 A, (19.2 W Max.)
	-20 ~ 50 °C / -4 ~ 122 °F
	0 ~ 85% RH (non-condensing)
	Indoor use
	174 x 145 x 40 mm / 6.85 x 5.7 x 1.57 in
	0.73 kg / 1.61 lb
	CE, FCC, RCM, RoHS compliant
	GV-VMS (V16.10.3.0), GV-DVR / NVR (V8.7.1.0), GV-Control Center (V3.4.0.0), GV-Edge Recording Manager (V1.2.0.0), GV-Center V2 (V16.10.0.0),
	GV-Recording Server (V1.3.0.0), GV-Redundant / Failover Server (V1.1.0.0)
	GV-Eye for iOS and Android
	GV-Eye for iOS and Android  IE, Firefox, Chrome, Safari, Edge
	Input

#### Note:

GV-VS2400

- 1. The GV-Video Server cannot work with the microphones that acquire power from the unit. Use microphones that have external power supply.
- 2. GV-VS2400 supports 1 external hard disk (2.5" or 3.5") with up to 4 TB capacities.
- 3. It is not recommended to use the flash USB drive with GV-VS2400 because of its slow read and write speed.
- 4. Product design and specifications are subject to change without notice.
- 5. When transmitting video signals over a long distance, it is highly recommended to use 5C-FB coaxial cables or above to minimize the degradation of image quality. The transmission distance should be within 300 m (984 ft).

-2-



### **Packing List**

- 1. GV-VS2400
- 2. AC Power Cord x 1
- 3. Power Adaptor x 1
- 4. GV-Video Server Software CD/DVD x 1
- 5. GV-NVR Software CD/DVD x 1
- 6. Warranty Card

### **Options**

Optional devices can expand your GV-Video Server's capabilities and versatility. Contact your dealer for more information.

optional devices can expand your G	V-Video Server's capabilities and versatility. Contact your dealer for more information.
	DC Male-to-Male Cable and DC 1-Male to 4-Female Cable are both used to power on the cameras through the GV-Video Server.
	For instance, you can purchase four DC Male-to-Male Cables and one DC 1-Male to 4-Female
DC Male-to-Male Cable	Cable to power on four cameras through the GV-Video Server.
DC 1-Male to 4-Female Cable	DC 1-Male to 4-Female Cable DC Male-to-Male Cable
GV-Relay V2	Working with the GV-Relay V2, the GV-Video Server is capable of driving the loads of relay outputs over 5 volts.
GV-WiFi Adaptor V2	The WiFi Adaptor V2 is designed to connect the GV IP devices, such as GV-Video Server, to the wireless network.
3.5 mm Stereo to RCA Cable	3.5 mm Stereo to RCA Cable is served as an audio adapter for microphones with RCA connectors.
Wall Hook	Wall Hook is used to mount GV-VS2400 to the wall.
DIN-rail Hook	DIN-rail Hook is used to mount GV-VS2400 to a 35-mm (1.38-in) DIN rail.
Rack Mount	Rack Mount is used to mount up to 3 video servers to a 19-in (482.6-mm) rack.

-3-



## **Supported Wireless LAN USB Adaptor**

Vendors	Model		
D-Link	DWA-140 (H/W version B1), DWL-G122 (version C1)		
EDIMAX	EW-7318Ug, EW-7718Un, EW-7711UAn		
Linksys	WUSB54GC, WUSB600 (version 1)		
Pegatron	WL-166N11		
Note: Linksys WUSB54GC ver. 3 is not supported.			

#### **Supported Mobile Broadband Device**

upported Mobile Bi	Todubaliu Device
Vendors	Model
Bandluxe	C320, C501
HUAWEI	E156, E156B, E169, E220, E1692, E1750, E1752, E1756, E1756C, EC169C, EC189 USB Modem
	(HSDPA/UMTS/EDGE/GPRS/GSM)
Novatel	MC950D, MC996D, MC998D (HSDPA/UMTS/EDGE/GPRS/GSM)
Onda	MSA523HS
Sierra	250U
Verizon	USB727, USB728, USB760 Modem (EVDO)
Vodafone	K3565 (Rev 2)
ZTE	MF100