



390/391 - iCLASS SE/Other HF - Combination Card Ordering Guide

The SIO-Enabled iCLASS with MIFARE or DESFire contactless smart card offers multiple High Frequency technologies to simplify card issuance for diverse systems or migration projects. Add new applications while leveraging your investment in existing access control systems. Personalize the card with a photo ID, magnetic stripe, barcode, or anti-counterfeiting element. This card offers maximized compatibility with added security into installations that DO not contain standard iCLASS or MIFARE/DESFire credentials.

Ensure each required option has been checked with the appropriate choice to fulfill a completed order form.

Base Model ☐ 390 Standard PVC ☐ 391 Composite 40% Polyester / PVC *

iCLASS Memory Size and Allocation (Check One)

- ☐ 0 - 2k Bits (256 Bytes) with 2 Application Areas (only available with MIFARE CLASSIC 1K)
- ☐ 3 - 32k Bits (4K Bytes) Application areas 16k/2+16k/1
- ☐ 4 - 32k Bits (4K Bytes) Application areas 16k/16+16k/1

Card Programming (Check One)

- ☐ R - SIO Programmed iCLASS & 2nd Technology. Specify Programming Information –
- ☐ P - Programmed iCLASS with SIO only not 2nd Technology. Specify Programming Information.
- ☐ A - Configured, Non-Programmed iCLASS, SIO Programmed 2nd Technology. Specify Programming Information.

2nd High Frequency Technology (Check One)

- ☐ M - MIFARE 1K Bytes (only available with iCLASS 2k bits)
- ☐ N - MIFARE 4K Bytes
- ☐ K - DESFire EV1 8K Bytes

Front Packaging (Check One)

- ☐ G - Plain White with Gloss Finish
- ☐ C - Custom Artwork with Gloss Finish – Specify Custom Artwork Number¹

Back Packaging (Check One)

- ☐ G - Plain White with Gloss Finish²
- ☐ C - Custom Artwork with Gloss Finish – Specify Custom Artwork Number¹
- ☐ 1 - Plain White with Gloss Finish with Magnetic Stripe²
- ☐ 3 - Custom Artwork with Gloss Finish with Magnetic Stripe – Specify Custom Artwork Number¹

iCLASS Card Numbering³ (Check One)

- ☐ M - Sequential Matching Internal/External (Inkjetted)⁶
- ☐ N - No External Card Numbering
- ☐ S - Sequential Internal/Sequential Non-Matching External (Inkjetted)⁶
- ☐ R - Random Internal/Non-Matching Sequential External (Inkjetted)⁶
- ☐ A - Sequential Matching Internal/External (Laser Engraved)⁴
- ☐ B - Sequential Internal/Sequential Non-Matching External (Laser Engraved)⁴
- ☐ C - Random Internal/Non-Matching Sequential External (Laser Engraved)⁴

Slot Punch⁵ (Check One)

IMPORTANT – Dual High Frequency credentials do not allow a slot punch due to the antenna design. HID recommends using a badge holder to attach this card to a lanyard or badge clip.

- ☒ N - No Slot Punch

2nd High Frequency Technology Card Numbering³ (Check One)


- ☐ M - Sequential Matching Internal/External (Inkjetted)⁶
- ☐ N - No External Card Numbering
- ☐ S - Sequential Internal/Sequential Non-Matching External (Inkjetted)⁶
- ☐ R - Random Internal/Non-Matching Sequential External (Inkjetted)⁶
- ☐ A - Sequential Matching Internal/External (Laser Engraved)⁴
- ☐ B - Sequential Internal/Sequential Non-Matching External (Laser Engraved)⁴
- ☐ C - Random Internal/Non-Matching Sequential External (Laser Engraved)⁴

Option - Custom Artwork¹

- ☐ _____ (Specify Artwork Number – Refer to the Custom Artwork Forms for new artwork)

Enter your final card options from the above selections. Example: 3904RNGCMNM

Final Part Number								N		-	(Options #)
-------------------	--	--	--	--	--	--	--	---	--	---	-------------



12345 = Card ID Number
YYYYYYY-YY = Sales Order Number