


DS-2CE55C2N


720TVL Picadis Indoor Dome Camera



Key Features

- 1/3" Picadis
- 1.3 MP Sensor: 1280 (H) x 960 (V) Effective Pixels
- 720 TVL Horizontal Resolution
- Electronic Day/Night
- 2.8 mm/3.6 mm/6 mm Fixed Lens, 0.1 lux @ $f/1.2$
- High Dynamic Range
- Superior Video Image Output and Ultra Low Light Illumination
- Wide Operating Temperature Range

Dimensions



Order Models

DS-2CE55C2N

DS-2CE55C2N	
Camera	
Image Sensor	1/3" Picadis
Signal System	NTSC
Effective Pixels	1280 (H) x 960 (V)
Minimum Illumination	0.1 lux @ ($f/1.2$, AGC on)
Shutter Speed	1/30 s to 1/30,000 s
Lens	3.6 mm (2.8 mm, 6 mm optional)
	Angle of view: 71.4° (3.6 mm)
Lens Mount	M12
Angle Adjustment	Pan: 0 to 355°, tilt: 0 to 90°, rotation: 0 to 355°
Day/Night	Electronic
Horizontal Resolution	720 TVL
Synchronization	Internal synchronization
Video Output	1 Vp-p composite output (75 Ω /BNC)
S/N Ratio	More than 62 dB
General	
Working Temperature/Humidity	-40° C to 60° C (-40° F to 140° F) Humidity 90% or less (non-condensing)
Power Supply	12 VDC
Power Consumption	Maximum 1 W
Dimensions	Ø97.8 mm x 64.4 mm (Ø3.85" x 2.54")
Weight	300 g (0.66 lb)