

DATA SHEET

ARUBA 3810 SWITCH SERIES

PRODUCT OVERVIEW

The Aruba 3810 Switch Series is an industry-leading mobile campus access solution for enterprises, SMBs, and branch office networks. With HPE Smart Rate multi-gigabit ports for high-speed IEEE 802.11ac devices, the Aruba 3810 will prepare your network for tomorrow. Right-size deployment and back haul capacity with modular 10GbE and 40GbE uplinks.

Full PoE+ provisioning available on 48-ports. Dual, redundant, hot-swappable power supplies and innovative backplane stacking technology delivers resiliency and scalability in a convenient 1U form factor. Advanced Layer 2 and 3 feature set with OSPF, IPv6, IPv4 BGP, Tunnel node, robust QoS, and policy-based routing are included with no software licensing.

With support for OpenFlow, the Aruba 3810 is ready to take advantage of SDN applications such as HPE Network Visualizer, HPE Network Optimizer, and HPE Network Protector applications. Easy to deploy and manage with advanced security and network management tools like Aruba ClearPass Policy Manager and Aruba AirWave. With support from Aruba Central, you can quickly set up remote branch sites with little or no IT support.

FEATURES AND BENEFITS

Software-defined networking

- OpenFlow is a key technology that enables SDN by allowing separation of the data (packet forwarding) and control (routing decision) paths

Unified wired and wireless

- Aruba ClearPass Policy Manager provides profiling, authentication, and policy management across multi-vendor wired and wireless networks
- HTTP redirect function supports HPE Intelligent Management Center (IMC) bring your own device (BYOD) solution
- Switch auto-configuration automatically configures switch for different settings such as VLAN, CoS, PoE max power, and PoE priority when Aruba AP is detected
- User Role defines a set of switch-based policies in areas such as security, authentication, and QoS. A user role can be assigned to a group of users or devices, using switch-based local user role or download from ClearPass



KEY FEATURES

- Advanced Layer 3 switch series with backplane stacking, Tunnel Node, low latency and resiliency
- Security and network management tools with Aruba ClearPass Policy Manager, AirWave and Central support
- Modular line rate 10GbE and 40GbE ports for wireless aggregation
- HPE Smart Rate for high-speed multi-gigabit bandwidth (IEEE 802.3bz) and PoE+ power
- Optimized for innovative SDN applications with OpenFlow support
- Tunnel Node provides a secure tunnel that transports network traffic on a per-port or per-user role basis to an Aruba Controller. In a per-user role Tunnel Node, users are authenticated by the ClearPass Policy Manager which directs traffic to be tunneled to an Aruba controller or switch locally
- Static IP Visibility allows ClearPass to do accounting for clients with static IP address

Quality of Service (QoS)

- Advanced classifier-based QoS classifies traffic using multiple match criteria based on Layer 2, 3, and 4 information; applies QoS policies such as setting priority level and rate limit to selected traffic on a per-port or per-VLAN basis
- Layer 4 prioritization enables prioritization based on TCP/UDP port numbers
- Class of Service (CoS) sets the IEEE 802.1p priority tag based on IP address, IP Type of Service (ToS), Layer 3 protocol, TCP/UDP port number, source port, and DiffServ

SPECIFICATIONS			
	Aruba 3810M 48G PoE+ 1-slot Switch (JL074A)	Aruba 3810M 16SFP+ 2-slot Switch (JL075A)	Aruba 3810M 40G 8 HPE Smart Rate PoE+ 1-slot Switch (JL076A)
Included accessories			
	1 Aruba 3810 Switch Fan Tray (JL088A)	1 Aruba 3810 Switch Fan Tray (JL088A)	1 Aruba 3810 Switch Fan Tray (JL088A)
I/O ports and slots			
	48 RJ-45 autosensing 10/100/1000 PoE+ ports (IEEE 802.3 Type 10BASE-T, IEEE 802.3u Type 100BASE-TX, IEEE 802.3ab Type 1000BASE-T, IEEE 802.3at PoE+); Duplex: 10BASE-T/100BASE-TX: half or full; 1000BASE-T: full only; Ports 1 – 48 support MACSec 1 open module slot Supports a maximum of 4 SFP+ ports or 2 40GbE ports, with optional module or 4 Smart Rate ports	16 SFP+ fixed 1000/10000 SFP+ ports; Duplex: 100BASE-TX: half or full; 1000BASE-T: full only; Ports 1 – 16 support MACSec 2 open module slots Supports a maximum of 8 SFP+ ports or 2 40GbE ports, with optional module or 4 Smart Rate ports	40 RJ-45 autosensing 10/100/1000 PoE+ ports (IEEE 802.3 Type 10BASE-T, IEEE 802.3u Type 100BASE-TX, IEEE 802.3ab Type 1000BASE-T, IEEE 802.3at PoE+); Duplex: 10BASE-T/100BASE-TX: half or full; 1000BASE-T: full only; Ports 1 – 40 support MACSec 8 RJ-45 HPE Smart Rate Multi-Gigabit ports; Ports 1 – 8 support MACSec 1 open module slot Supports a maximum of 4 SFP+ ports or 2 40GbE ports, with optional module or 4 Smart Rate ports
Additional ports and slots			
	1 stacking module slot 1 RJ-45 serial console port 1 RJ-45 out-of-band management port 1 dual-personality (RJ-45 or USB micro-B)	1 stacking module slot 1 RJ-45 serial console port 1 RJ-45 out-of-band management port 1 dual-personality (RJ-45 or USB micro-B)	1 stacking module slot 1 RJ-45 serial console port 1 RJ-45 out-of-band management port 1 dual-personality (RJ-45 or USB micro-B)
Power supplies			
	2 power supply slots 1 minimum power supply required (ordered separately)	2 power supply slots 1 minimum power supply required (ordered separately)	2 power supply slots 1 minimum power supply required (ordered separately)
Fan tray			
	Includes: 1 x JL088A 1 fan tray slot Switch ships with 1 JL088A fan tray installed. Spares ordered separately.	Includes: 1 x JL088A 1 fan tray slot Switch ships with 1 JL088A fan tray installed. Spares ordered separately.	Includes: 1 x JL088A 1 fan tray slot Switch ships with 1 JL088A fan tray installed. Spares ordered separately.
Physical characteristics			
Dimensions	17.42(w) x 16.98(d) x 1.73(h) in (44.25 x 43.13 x 4.39 cm) (1U height)	17.42(w) x 16.98(d) x 1.73(h) in (44.25 x 43.13 x 4.39 cm) (1U height)	17.42(w) x 16.98(d) x 1.73(h) in (44.25 x 43.13 x 4.39 cm) (1U height)
Weight	13.62 lb (6.18 kg)	13.28 lb (6.02 kg)	13.61 lb (6.17 kg)
Memory and processor			
	P2020 Dual Core @ 1.2 GHz, 4 GB DDR3 SDRAM, 1 GB SD Card	P2020 Dual Core @ 1.2 GHz, 4 GB DDR3 SDRAM, 1 GB SD Card	P2020 Dual Core @ 1.2 GHz, 4 GB DDR3 SDRAM, 1 GB SD Card
	Dual ARM Coretex A9 @ 1 GHz, 2 GB DDR3 SDRAM; Packet buffer size: 13.5 MB Internal	Dual ARM Coretex A9 @ 1 GHz, 2 GB DDR3 SDRAM; Packet buffer size: 13.5 MB Internal	Dual ARM Coretex A9 @ 1 GHz, 2 GB DDR3 SDRAM; Packet buffer size: 13.5 MB Internal

SPECIFICATIONS

	Aruba 3810M 48G PoE+ 1-slot Switch (JL074A)	Aruba 3810M 16SFP+ 2-slot Switch (JL075A)	Aruba 3810M 40G 8 HPE Smart Rate PoE+ 1-slot Switch (JL076A)
Mounting and enclosure			
	Mounts in an EIA-standard 19 in. telco rack or equipment cabinet (hardware included); Horizontal surface mounting only	Mounts in an EIA-standard 19 in. telco rack or equipment cabinet (hardware included); Horizontal surface mounting only	Mounts in an EIA-standard 19 in. telco rack or equipment cabinet (hardware included); Horizontal surface mounting only
Performance			
	IPv6 Ready Certified	IPv6 Ready Certified	IPv6 Ready Certified
1000 Mb Latency	< 2.8 µs (FIFO 64-byte packets)	< 2.8 µs (FIFO 64-byte packets)	< 2.8 µs (FIFO 64-byte packets)
10 Gbps Latency	< 1.8 µs (FIFO 64-byte packets)	< 1.8 µs (FIFO 64-byte packets)	< 1.8 µs (FIFO 64-byte packets)
40 Gbps Latency	< 1.5 µs (FIFO 64-byte packets)	< 1.5 µs (FIFO 64-byte packets)	< 1.5 µs (FIFO 64-byte packets)
Throughput	up to 190.5 Mpps (64-byte packets)	up to 285.7 Mpps (64-byte packets)	up to 273.8 Mpps (64-byte packets)
Routing/Switching capacity	320 Gbps	480 Gbps	480 Gbps
Switch fabric speed	338 Gbps	508 Gbps	508 Gbps
Routing table size	10000 entries (IPv4), 5000 entries (IPv6)	10000 entries (IPv4), 5000 entries (IPv6)	10000 entries (IPv4), 5000 entries (IPv6)
MAC address table size	64000 entries	64000 entries	64000 entries
Environment			
Operating temperature	32°F to 113°F (0°C to 45°C)	32°F to 113°F (0°C to 45°C)	32°F to 113°F (0°C to 45°C)
Operating relative humidity	15% to 95% @ 104°F (40°C), noncondensing	15% to 95% @ 104°F (40°C), noncondensing	15% to 95% @ 104°F (40°C), noncondensing
Nonoperating/Storage temperature	-40°F to 158°F (-40°C to 70°C)	-40°F to 158°F (-40°C to 70°C)	-40°F to 158°F (-40°C to 70°C)
Nonoperating/Storage relative humidity	15% to 90% @ 149°F (65°C), noncondensing	15% to 90% @ 149°F (65°C), noncondensing	15% to 90% @ 149°F (65°C), noncondensing
Altitude	up to 10,000 ft (3 km)	up to 10,000 ft (3 km)	up to 10,000 ft (3 km)
Acoustic	Power: 42 dB, Pressure: 26 dB	Power: 39 dB, Pressure: 22.3 dB	Power: 45 dB, Pressure: 27.9 dB
Safety			
	EN 60950/IEC 60950; UL 60950; UL 60950-1; CAN/CSA 22.2 No. 60950; EN 60825; CSA 22.2 60950-1; EN62479:2010; EN 60950-1:2006 +A11:2009 +A1:2010 +A12:2011+A2:2013; EN 62368-1, Ed. 2; IEC 60950-1:2005 Ed.2; Am 1:2009+A2:2013; IEC 60825:2007; EN60850-1:2007 / IEC 60825-1: 2007 Class1 Class 1 Laser Products / Laser Klasse 1; UL 62368-1 Ed.2	EN 60950/IEC 60950; UL 60950; UL 60950-1; CAN/CSA 22.2 No. 60950; EN 60825; CSA 22.2 60950-1; EN62479:2010; EN 60950-1:2006 +A11:2009 +A1:2010 +A12:2011+A2:2013; EN 62368-1, Ed. 2; IEC 60950-1:2005 Ed.2; Am 1:2009+A2:2013; IEC 60825:2007; EN60850-1:2007 / IEC 60825-1: 2007 Class1 Class 1 Laser Products / Laser Klasse 1; UL 62368-1 Ed.2	EN 60950/IEC 60950; UL 60950; UL 60950-1; CAN/CSA 22.2 No. 60950; EN 60825; CSA 22.2 60950-1; EN62479:2010; EN 60950-1:2006 +A11:2009 +A1:2010 +A12:2011+A2:2013; EN 62368-1, Ed. 2; IEC 60950-1:2005 Ed.2; Am 1:2009+A2:2013; IEC 60825:2007; EN60850-1:2007 / IEC 60825-1: 2007 Class1 Class 1 Laser Products / Laser Klasse 1; UL 62368-1 Ed.2

SPECIFICATIONS			
	Aruba 3810M 48G PoE+ 1-slot Switch (JL074A)	Aruba 3810M 16SFP+ 2-slot Switch (JL075A)	Aruba 3810M 40G 8 HPE Smart Rate PoE+ 1-slot Switch (JL076A)
Emissions			
	FCC Class A; VCCI Class A; EN 55022/CISPR 22 Class A; EN 60950-1:2006 +A11:2009 +A1:2010 +A12:2011+A2:2013	FCC Class A; VCCI Class A; EN 55022/CISPR 22 Class A; EN 60950-1:2006 +A11:2009 +A1:2010 +A12:2011+A2:2013	FCC Class A; VCCI Class A; EN 55022/CISPR 22 Class A; EN 60950-1:2006 +A11:2009 +A1:2010 +A12:2011+A2:2013
Immunity			
Generic	EN55022: 2010	EN55022: 2010	EN55022: 2010
EN	EN55024: 2010	EN55024: 2010	EN55024: 2010
ESD	IEC 61000-4-2	IEC 61000-4-2	IEC 61000-4-2
Radiated	IEC 61000-4-3; 3 V/m	IEC 61000-4-3; 3 V/m	IEC 61000-4-3; 3 V/m
EFT/Burst	IEC 61000-4-4; 1.0 kV (power line), 0.5 kV (signal line)	IEC 61000-4-4; 1.0 kV (power line), 0.5 kV (signal line)	IEC 61000-4-4; 1.0 kV (power line), 0.5 kV (signal line)
Surge	IEC 61000-4-5; 1 kV/2 kV AC	IEC 61000-4-5; 1 kV/2 kV AC	IEC 61000-4-5; 1 kV/2 kV AC
Conducted	IEC 61000-4-6; 3 V	IEC 61000-4-6; 3 V	IEC 61000-4-6; 3 V
Power frequency magnetic field	IEC 61000-4-8; 1 A/m, 50 or 60 Hz	IEC 61000-4-8; 1 A/m, 50 or 60 Hz	IEC 61000-4-8; 1 A/m, 50 or 60 Hz
Voltage dips and interruptions	IEC 61000-4-11; >95% reductions, 0.5 period; 30% reduction, 25 periods	IEC 61000-4-11; >95% reductions, 0.5 period; 30% reduction, 25 periods	IEC 61000-4-11; >95% reductions, 0.5 period; 30% reduction, 25 periods
Harmonics	EN61000-3-2:2006 +A1:2009 +A2:2009 Class A	EN61000-3-2:2006 +A1:2009 +A2:2009 Class A	EN61000-3-2:2006 +A1:2009 +A2:2009 Class A
Flicker	EN61000-3-3:2008	EN61000-3-3:2008	EN61000-3-3:2008
Management			
	Aruba Central; Aruba AirWave Network Management; IMC – Intelligent Management Center; Command-line interface; Web browser; Configuration menu; Out-of-band management (RJ-45 Ethernet); In-line and out-of-band; Out-of-band management (serial RS-232c or micro usb)	Aruba Central; Aruba AirWave Network Management; IMC – Intelligent Management Center; Command-line interface; Web browser; Configuration menu; Out-of-band management (RJ-45 Ethernet); In-line and out-of-band; Out-of-band management (serial RS-232c or micro usb)	Aruba Central; Aruba AirWave Network Management; IMC – Intelligent Management Center; Command-line interface; Web browser; Configuration menu; Out-of-band management (RJ-45 Ethernet); In-line and out-of-band; Out-of-band management (serial RS-232c or micro usb)
Services			
	Refer to the Hewlett Packard Enterprise website at www.hpe.com/networking/services for details on the service-level descriptions and product numbers. For details about services and response times in your area, please contact your local Hewlett Packard Enterprise sales office.	Refer to the Hewlett Packard Enterprise website at www.hpe.com/networking/services for details on the service-level descriptions and product numbers. For details about services and response times in your area, please contact your local Hewlett Packard Enterprise sales office.	Refer to the Hewlett Packard Enterprise website at www.hpe.com/networking/services for details on the service-level descriptions and product numbers. For details about services and response times in your area, please contact your local Hewlett Packard Enterprise sales office.