

CLAMPING RACKSHELF, 7 RU

CAP7 |



FEATURES & BENEFITS

Captivate components with CAP Series clamping rackshelves. Rubber-lined clamps secure a component from the top. Adjustable rear “L” brackets prevent units from being pushed back. Vented bottoms with a robust 16-gauge steel design that maintains structural integrity in mobile applications. Finished in a durable black powder coat. Useable shelf area is 17.38”w x 15.10”d.



- Clamping shelf holds components securely with rubber-lined clamps
- Vented sides and bottom for efficient cooling
- Robust steel construction with black powder coat finish
- Ships ready-to-assemble to save space

SPECIFICATIONS

GENERAL INFO

Finish: Black Powder Coat
UL Standards Tested: 1678

ASSEMBLY/INSTALLATION INFORMATION

Mounting Points: 2

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
Greenguard: Yes

DIMENSIONS

Usable Depth: 15.1
Capacity Weight (US): 100

Depth (US): 15.37
Height (US): 12.25
Width (US): 19
Rack Units: 7

TECHNICAL INFORMATION

Static Load Capacity: 100
Material: Steel