

Chisels

Electrician's Chisel

- One-piece handle and blade forged of strong alloy steel
- Corrosion-resistant black finish extends to the polished blade edge



66100

Cat. No.	Blade Width	Overall Length	Weight
66100	2-3/4" (69.9 mm)	8" (203.2 mm)	1.1 lbs. (0.50 kg)

Punches

Drift Punches

- High-carbon steel for durability
- Rugged design for impact strength
- Strong, heat-treated points are smooth and precision tapered
- Corrosion-resistant black finish



66343

Cat. No.	Point Diameter	Taper	Overall Length	Weight
66340	0.125" (3.18 mm)	4-1/4" (108.0 mm)	8" (203.2 mm)	3.2 oz. (91 g)
66342	0.188" (4.76 mm)	5" (127.0 mm)	9" (228.6 mm)	5.6 oz. (159 g)
66343	1/4" (6.4 mm)	5-1/2" (139.7 mm)	11" (279.4 mm)	12.0 oz. (340 g)
66344	0.313" (7.9 mm)	5-1/2" (139.7 mm)	11" (279.4 mm)	12.0 oz. (340 g)

Center Punches

- High-carbon steel for durability
- Rugged design for impact strength
- Smooth-ground points heat-treated to stay sharp and true longer
- Corrosion-resistant black finish



66313

Cat. No.	Shank Diameter	Overall Length	Weight
66310	1/4" (6.4 mm)	4-1/4" (108.0 mm)	0.8 oz. (23 g)
66311	5/16" (7.9 mm)	4-1/2" (114.3 mm)	1.6 oz. (45 g)
66312	3/8"	5" (127.0 mm)	1.6 oz. (45 g)
66313	1/2" (12.7 mm)	6" (152.4 mm)	4.0 oz. (113 g)

Pin Punches

- High-carbon steel for durability
- Precision-ground shank
- Heat-treated for added strength and hardness at working end
- Corrosion-resistant black finish



66324

Cat. No.	Point Diameter	Overall Length	Weight
66320	.063" (1.59 mm)	4-1/4" (108.0 mm)	0.8 oz. (23 g)
66321	.094" (2.4 mm)	4-3/4" (120.7 mm)	1.6 oz. (45 g)
66322	0.125" (3.18 mm)	5" (127.0 mm)	1.6 oz. (45 g)
66323	0.156" (3.97 mm)	5-1/4" (133.4 mm)	1.6 oz. (45 g)
66324	0.188" (4.76 mm)	5-1/2" (139.7 mm)	1.6 oz. (45 g)
66325	1/4" (6.4 mm)	7" (177.8 mm)	3.2 oz. (91 g)

