



GoControl Product Specification Chart


SMART SENSORS


Part Number	Description		Z-Wave Range (line of sight)	Operating Temp.
WAPIRZ-1	Passive Infrared Motion Detector	-	Up to 100'	5° - 140° F
WADWAZ-1	Door-Window Sensor	-	Up to 100'	5° - 140° F
WA105DBZ-1	Siren/Strobe Warning Device	-	Up to 100'	5° - 140° F
GB00Z-2	Glass Break Sensor	-	Up to 100'	32° to 120° F
WF00Z-1	Water Leak Sensor	✓	Up to 130'	32° to 120° F

SMART CONTROL

Part Number	Description		Z-Wave Range (line of sight)	Operating Temp.
GD00Z-4	Garage Door Opener Remote Controller	✓	Up to 130'	-4° to 122° F
GC-TBZ48	Battery-powered Smart Thermostat	-	Up to 100'	32° to 120°F

SMART ELECTRICAL

Part Number	Description		Brightness
LB60Z-1	Dimmable LED Standard Light Bulb (60-watt equivalent)	✓	750 lumens
LBR30Z-1	Dimmable LED Flood Light Bulb (65-watt equivalent)	✓	650 lumens
LB65R6Z-1	Retrofit Recessed LED Light Bulb Kit (65-watt equivalent)	✓	650 lumens

Part Number	Description		Isolated Contacts/Resistive	Motor
WD1000Z-1	In-Wall Dimmer Switch, 1000 W	-	n/a	n/a
WD500Z5-1	In-Wall Dimmer Switch, 500 W	✓	n/a	n/a
WT00Z5-1	In-Wall Wireless "3-Way" switch	✓		None (does not control motor)
WS15Z5-1	In-Wall Switch	✓	15 amps, 1800W max	1/2 H.P. maximum, 120 VAC
WO15EMZ5-1	In-Wall Receptacle Outlet	✓	15 amps, 1800W max	1/2 H.P. maximum, 120 VAC
PD300EMZ5-1	Smart EM Lamp Module	✓	n/a	n/a
PS15EMZ5-1	Smart EM Appliance Module	✓	15 amps, 1800W max	15 amps, 1800W max
FS20Z-1	Fixture-Mounted Control Module	-	20 amps G.P. max, 277 VAC, 10 FLA, 60 LRA, 250 VAC	1 H.P. max, 120/240 VAC
WA00Z-1	Battery-powered Scene Controller	✓		None (does not control motor)



PD300EMZ5-1

Smart EM Lamp Module

Quickly add dimmable control to a lamp with the EM Lamp Module. A simple plug-n-play device, lighting control has never been easier or Greener. It's unique Energy Monitoring circuitry provides both a visual indication of the amount of energy being used, as well as reports it to the Z-Wave hub for reference. It will also light your path with an integrated LED night light.

- Energy Monitoring reports energy usage
- Does not impede 2nd outlet



PS15EMZ5-1

Smart EM Appliance Module

Remotely control devices with the EM Appliance Module. Plug in the tea kettle, light or small appliance and activate it on a schedule, from your phone or Smart Switch. And with Energy Monitoring capability, know how Green your appliances are performing. It will also light your path with an integrated LED night light.

- Energy Monitoring reports energy usage
- Does not impede 2nd outlet
- 15 Amp maximum capacity



FS20Z-1

Smart Fixture Module

GoControl's Isolated Contact Fixture Module can be mounted in a single- or multi-gang electrical box to operate loads or control relay-based devices. The relay can be isolated for dry contact applications or powered to switch live loads. This device can operate loads of up to 277v.

Possible Applications: Commercial Lighting, In-Ceiling Lighting/fans, Dry-Contact Relays, Pool Pumps, Water Heaters, Fireplaces.

