

TECH-SPEC:

Product Reference Sheet

4131_RL_

Example: **4131 | C | RL | 36**
 Profile# Finish Insert Length

CATEGORY: Door Bottoms

TYPE: Automatic Door Bottoms

FINISHES: C (Clear Anodized), D (Dark Anodized)


LENGTHS: 24" to 48"

WIDTH: 19/32" (15.08 mm)

HEIGHT: 1-27/32" (48.8 mm)

WEIGHT: Estimated per foot: 0.50 lbs

RATINGS:       



PRODUCT APPROVALS:

- 4131_RL has been tested and approved under ULI10C for Fire; ULI1784 for smoke
- BHMA A156.21
- ASTM E-283 for Air Infiltration
- ASTM E-90-97 and ASTM E1408-91 for Sound Control
- Category J and H gaskets for use with classified steel covered composite, hollow metal doors rated up to and including 3 hours; wood and plastic covered composite doors rated up to and including 1-1/2 hours; and wood core doors rated for 20 minutes without hose stream.

ANSI NUMBER: R3C345

LEAD TIME: 4 working days (or less)

AVAILABLE: 4131_RL_ is shipped from PEMKO's Memphis, Ventura, Vancouver and Toronto locations

CROSS REFERENCE: Draftseal: DS335CR; Hager: 740SN; NGP: 222N, 223N; Reese: 321; K N Crowder: CT-50

INSTRUCTIONS: Available upon request (and on website)

CAD DRAWINGS: Available upon request (and on website)

PROFILE DRAWINGS: Available upon request (and on website)

CUT SHEET: Available upon request (and on website)

www.pemko.com

Memphis, TN USA
 P.O. Box 18966
 Memphis, TN 3818
 P: 800.824.3018
 F: 800.243.3656

Ventura, CA USA
 P.O. Box 3780
 Ventura, CA 93006
 P: 800.283.9988
 F: 800.283.4050

Vancouver, BC Canada
 103-2480 Mt. Lehman Rd.
 Abbotsford, BC V2T 6W3
 P: 877.535.7888
 F: 877.535.7444

Toronto, ON Canada
 160 Four Valley Dr.
 Vaughan, ON L4K 4T9
 P: 877.535.7888
 F: 877.535.7444