



C81638-000 | FOSC450-D6-6-36-1-D3V

**FOSC™450 D6 Fiber Optic Splice Closure, Gel Cable sealing, one pre-installed 36-splice tray, with test valve**

- Single-ended, O-ring sealed dome closure for splicing feeder and distribution cables
- Gel cable sealing technology allows easy adding or removing of a wide size range of cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- FOSC splice trays hinged for access to any splice without disturbing other trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

## Product Classification

Brand	FOSC™
Product Series	FOSC 450
Product Type	Butt feeder and distribution closure
Regional Availability	Latin America   North America

## Body Features

Cable Seal	Compressed Gel
Color	Black

## Configuration Features

Port Shape	Round (6)
Flash Test Valve	Yes
Number of Pre-installed Splice Trays	36-fiber (1)
Ground Feedthrough	Yes
Ground Feedthrough Lugs	3
Number of Cable Attachments	6
Slack Basket	Yes


## Dimensions

Closure Diameter	292.000 mm   11.496 in
Length	753.00 mm   29.65 in

## Operation/Application

Environment	Direct burial   Manholes
-------------	--------------------------

## Outline Drawing



## Packaging Features

Minimum Order Quantity	1
Packaging Method	Box/Carton

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant