


Pan-Way® TG-70 Surface Raceway System

specifications

TG non-metallic multi-channel surface raceway shall be used to route, protect and conceal data, voice, video, fiber optic and power cabling. The raceway shall be listed as suitable for use in applications up to 600 volts between conductors by Underwriters Laboratories, Inc. per standard 5A, and by Canadian Standards Association, Inc. per 22.2 no. 62.1-03, when screw secured and installed per instructions. A full complement of fittings with a 40mm (1.6") minimum bend radius compliant with TIA/EIA-568-B must be available as well as device brackets and internal junction boxes to install a variety of communication and electrical devices. Divider walls must be available to form separate channels in the multi-channel raceway. Panduit "snap-on" faceplates for data and power terminations shall be available. TG raceway will be manufactured from impact-resistant material with flammability rating of V-0. TG raceway must be tamper resistant, yet allow access for moves, adds and changes. TG raceway finish shall be pure color and will resist scratches and dents and will not peel or corrode. TG raceway shall be available in three standard colors and shall be optimized for use with the Panduit® Pan-Net® Communication System.



technical information

Material:	Rigid PVC
Flammability:	UL94V-0; FT4
Voltage rating:	UL-5A 600VAC; CSA C22.2 No. 62.1-03 600V
Approvals:	UL Listed 95425 (raceway); UL Listed E116129 (fittings); CE Listed
NEC:	Article 388
Color:	Off-White (IW) and Electrical Ivory (EI); International Gray (IG) available in 8' lengths only.
CSI spec form:	LP-CSISPEC-TG70-1

key features and benefits

Large cable capacity	Provides maximum cable routing space which allows for a large number of cables to be routed within a single raceway channel
40mm (1.6) bend radius control fittings	Increased bend radius control to satisfy the needs and maximizes the headroom of larger diameter high performance copper cable and fiber optic cabling
Snap-on faceplates	Faceplates snap directly onto the raceway base; cabling can be quickly accessed by removing only the faceplate, which requires less labor and lowers the cost of maintenance
Channel has a 70mm opening	Accepts any manufacturer's NEMA standard snap-on or screw-on power or communication faceplates
Non-metallic construction	Lightweight, reducing installer fatigue; solid color through out profile will not chip, peel, rust, corrode, or scratch; easy to cut reducing the need for special cutting devices; high impact resistance; durable
Designer profile	Aesthetically pleasing and matches a wide variety of decors
Available in three standard colors	Matches a variety of colors for various applications of decors

applications

Pan-Way® TG-70 Surface Raceway is a multi-channel channel raceway which provides a solution for routing low voltage, fiber optic and/or power cabling when maximum cable

capacity is required. TG-70 Raceway can mount NEMA standard screw-on faceplates or superior Pan-Way® Snap-On Faceplates directly to the channel.

Pan-Way® TG-70 Raceway

Raceway Base and Cover (packaged together)	
8 feet:	TG70IW8
10 feet:	TG70IW10
Replacement Cover	
8 feet:	T70CIW8
10 feet:	T70CIW10
Divider Wall	
8 feet:	TGDW8
10 feet:	TGDW10

TG-70 Raceway Fittings and Accessories


Base coupler:	TG70BCIW-X
Cover coupler:	T70CCIW-X
Adjustable outside corner fitting:	TGOCIW
Adjustable Inside corner fitting:	TGICIW
Non-adjustable inside corner fitting:	TGSICIW
Non-adjustable outside corner fitting:	TGSOCIW
Right angle fitting:	TGRAIW
End cap fitting:	TGECIW
Tee fitting:	TGTIW
Tee divider insert:	TGTD
Transition fitting:	TGTRIW
Wire retainer:	TG70WR-X
Device bracket:	T70DB-X
Three sided hanging box:	TG70HB3-X
GFCI three sided hanging box:	TG70HB3GFCI-X
Backfeed fitting:	TGBFIW
Backfeed fitting insert:	TGBFI
Entrance end fitting:	TGEEIW
Standard faceplate bracket:	T70SDB-X
Fiberspool bracket (2 halves):	TGFSB

For standard colors other than Off White (IW), replace IW in part number with EI (Electrical Ivory) or IG (International Gray). International Gray available in 8' lengths only.


Pan-Way® TG-70 Surface Raceway System

Wire Fill


Raceway Type and Configuration	Fill Area (in²)	Electrical Cables			Data Grade Cables										Coax Cables				Fiber Optic Cable								
		14 AWG	12 AWG	10 AWG	24 AWG	24 AWG	24 AWG	24 AWG	24 AWG	24 AWG	24 AWG	24 AWG	24 AWG	24 AWG	24 AWG	24 AWG	24 AWG	24 AWG	24 AWG	24 AWG	24 AWG	24 AWG	24 AWG	24 AWG	24 AWG	24 AWG	24 AWG
		THHN/THWN/T90			Cat. 5e – Plenum		Cat. 5e – Riser		Cat. 6		Cat. 6A		Cat. 6A		Cat. 6A		Cat. 6A (SD)		RG6		RG59/u		2 Strand				
		0.111	0.130	0.164	DIA = 0.193		DIA = 0.225		DIA = 0.240		DIA = 0.289		DIA = 0.300		DIA = 0.330		DIA = 0.240		DIA = 0.275		DIA = 0.242		DIA = 0.175				
		FILL			FILL		FILL		FILL		FILL		FILL		FILL		FILL		FILL		FILL		FILL				
		MAX	MAX	MAX	SPEC	MAX	SPEC	MAX	SPEC	MAX	SPEC	MAX	SPEC	MAX	SPEC	MAX	SPEC	MAX	SPEC	MAX	SPEC	MAX	SPEC	MAX	SPEC	MAX	
(UL Temp Rise Test)			(40%)	(60%)	(40%)	(60%)	(40%)	(60%)	(40%)	(60%)	(40%)	(60%)	(40%)	(60%)	(40%)	(60%)	(40%)	(60%)	(40%)	(60%)	(40%)	(60%)	(40%)	(60%)			
TG70: Data Only using Screw on Faceplates and Devices	10.09	**	**	**	137	206	101	152	89	133	61	92	57	85	47	70	89	133	67	101	87	131	167	251			
TG70: Data Only using Snap-on Faceplates and Wire Retainer	10.68	**	**	**	146	219	107	161	94	141	65	97	60	90	49	74	94	141	71	107	92	139	177	266			
TG70: Wire Retainer without Devices	10.85	40	40	38	148	222	109	163	95	143	66	99	61	92	50	76	95	143	73	109	94	141	180	270			
TG70: Divided Power and Data (A)	3.16	28	28	26	**	**	**	**	**	**	**	**	**	**	**	**	**	**	**	**	**	**	**	**			
TG70: Divided Power and Data (B)	7.20	**	**	**	98	147	72	108	63	95	43	65	40	61	33	50	63	95	48	72	62	93	119	179			
TG70: Power and Data using Snap-On Faceplates and 3 Sided Power Box (A)	3.08	28	28	26	**	**	**	**	**	**	**	**	**	**	**	**	**	**	**	**	**	**	**	**			
TG70: Power and Data using Snap-On Faceplates and 3 Sided Power Box (B)	5.58	**	**	**	76	114	56	84	49	74	34	51	31	47	26	39	49	74	37	56	48	72	92	139			



TG-70 Raceway




TG70




T70C (Replacement Cover)

Pan-Way® TG-70 Surface Raceway System


Fittings and Accessories




TG70BC-X




T70CC-X




TG0C




TGSOC




TGIC




TGSIC




TGRA



TGEC




TGT




TGTR




TGDW




TGTD




TG70WR-X




T70DB-X




TG70HB3-X



TG70HB3GFCI-X



TGBFI




TGBF



TGEE



TGFSB



T70SDB-X

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT®

©2015 Panduit Corp.
ALL RIGHTS RESERVED.
Printed in the U.S.A.
SRSP31-WW-ENG
Replaces WW-SRSP13
1/2015