


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



| PART NUMBER | VALVE SIZE<br>in. [mm]           | STANDARD<br>PKG. | MAX.<br>HANDLE<br>LENGTH | MAX<br>HANDLE<br>WIDTH | OPERATING<br>TEMPERATURE                 |
|-------------|----------------------------------|------------------|--------------------------|------------------------|------------------------------------------|
| PSL-BV2     | 1 1/1" - 2 1/2"<br>[38.1 - 68.5] | 1                | 10"<br>[254.0]           | 1.0"<br>[25.4]         | -40° F (-40° C)<br>TO<br>215° F (120° C) |



NOTES:  
1. MILLIMETERS  
SHOWN IN ( ).

|                                                                                                   |  |                                                                                               |  |
|---------------------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------------------------------|--|
| CAD FILENAME/LAYERS                                                                               |  | 100923CM_DC_C10644/00B                                                                        |  |
| PANDUIT                                                                                           |  | CORP. TINLEY PARK, ILLINOIS                                                                   |  |
| PSL-BV2 BALL VALVE LOCKOUT                                                                        |  |                                                                                               |  |
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE:<br>(.X) ± (.XXX) ±<br>(.XX) ± ANGLES ± |  | UNLESS OTHERWISE SPECIFIED,<br>ALL DIMENSIONS ARE GIVEN<br>IN INCHES, THIRD ANGLE PROJECTION. |  |
| DRAWN BY<br>RVU                                                                                   |  | MAT'L:<br>RED<br>POLYPROPYLENE<br>PANTONE PMS 186                                             |  |
| DATE<br>9-12-03                                                                                   |  | SCALE<br>NTS                                                                                  |  |
| CHK'G<br>HAC                                                                                      |  | DRAWING NO.<br>C10644                                                                         |  |
|                                                                                                   |  | DWG<br>A<br>SIZE                                                                              |  |

|     |          |      |                                                      |             |     |     |      |     |  |
|-----|----------|------|------------------------------------------------------|-------------|-----|-----|------|-----|--|
| I   | 12-13-10 | JHAC | ADDED OPERATING TEMPERATURES AND<br>MAX HANDLE WIDTH | 6256        |     |     |      |     |  |
| R   | 2/11/08  | RVU  | DRAWING RELEASE                                      | 5330        | R   |     |      |     |  |
| REV | DATE     | BY   | CHK                                                  | DESCRIPTION | ECN | - R | CUST | SUP |  |