

## AXIS P1365 Mk II Network Camera

Outstanding light sensitivity and Zipstream

AXIS P1365 Mk II offers outstanding light sensitivity, supporting Lightfinder and WDR – Forensic Capture, it optimizes the video for extreme levels of detail even in low-light and dark environments. Delivering HDTV 1080p video up to 50/60 fps with reduced noise and motion blur, the camera captures moving objects even in high-pace environments. Axis Zipstream analyzes and optimizes the video stream saving bandwidth and storage while maintaining video quality. AXIS P1365 Mk II includes the ability to seamlessly transition between WDR and Lightfinder. With a CS-mount, the camera supports a variety of lens options. AXIS T91B21 Stand allows for discreet cable management.

- > Light sensitive with Lightfinder Technology
- > Flexible CS-mount lens alternatives
- > Saving costs with Axis Zipstream
- > Up to 50/60 fps in HDTV 1080p
- > WDR Forensic Capture







## AXIS P1365 Mk II Network Camera

~	
Camera Image sensor	1/2.8" progressive scan PGR CMOS
Lens	1/2.8" progressive scan RGB CMOS IR corrected, CS-mount lens, P-Iris
Lens	Varifocal 2.8–8 mm, F1.3
	Horizontal field of view: 112°–39° Vertical field of view: 58°–21°
Day and night	Automatically removable infrared-cut filter
Minimum	Color: 0.11 lux
illumination	B/W: 0.01 lux, at 50 IRE F1.3 HDTV 1080p 50/60 fps: Color 0.22 lux
	<b>B/W:</b> 0.02 lux, at 50 IRE F1.3
Shutter time	1/66500 s to 2 s
Video	
Video compression	H.264 (MPEG-4 Part 10/AVC) Baseline, Main and High Profiles Motion JPEG
Resolution	HDTV 1080p 25/30 fps (WDR): 1920x1080 to 160x90 HDTV 1080p 50/60 fps (no WDR): 1920x1080 to 160x90
Frame rate	Up to 50/60 fps (50/60 Hz)
Video streaming	Multiple, individually configurable streams in H.264 and Motion JPEG
	Axis Zipstream technology in H.264
	Controllable frame rate and bandwidth VBR/MBR H.264
Multi-view	Up to 8 individually cropped out view areas
streaming	
Image settings	Compression, Color, Brightness, Sharpness, Contrast, Local
	contrast, White balance, Exposure control, Exposure zones, WDR - forensic capture: Up to 120 dB depending on scene, Fine tuning
	of behavior at low light, Rotation: 0°, 90°, 180°, 270° including
	Corridor Format, Text and image overlay, Privacy mask, Mirroring of images
Pan/Tilt/Zoom	Digital PTZ Uploadable PTZ driver (Pelco D pre-installed)
Audio	
Audio streaming	Two-way, full duplex
Audio	24bit LPCM, AAC LC 8/16/32/48 kHz, G.711 PCM 8 kHz,
compression	G.726 ADPCM 8 kHz Configurable bit rate
Audio	External microphone input or line input, line output, built-in
input/output	microphone (can be disabled)
Network	Password protection ID address filtering UTTDC3 approximation
Security	Password protection, IP address filtering, HTTPS <sup>a</sup> encryption, IEEE 802.1X <sup>a</sup> network access control, Digest authentication, User access log
Supported	IPv4/v6, HTTP, HTTPS <sup>a</sup> , SSL/TLS <sup>a</sup> , QoS Layer 3 DiffServ, FTP,
protocols	CIFS/SMB, SMTP, Bonjour, UPnP <sup>™</sup> , SNMP v1/v2c/v3 (MIB-II), DNS, DynDNS, NTP, RTSP, RTP, SRTP, SFTP, TCP, UDP, IGMP, RTCP, ICMP,
	DHCP, ARP, SOCKS, SSH, LLDP
System integra	tion
Application	Open API for software integration, including VAPIX®
Programming Interface	and AXIS Camera Application Platform, specifications at www.axis.com
	AXIS Video Hosting System (AVHS) with One-Click Connection
	ONVIF® Profile S and ONVIF® Profile G, specification at www.onvif.org
Analytics	AXIS Video Motion Detection, active tampering alarm, audio
-	detection
	Support for AXIS Camera Application Platform enabling installation of third-party applications, see www.axis.com/acap
Event triggers	Analytics, edge storage events, external input, audio level, time
	scheduled

Event actions	Record video: SD card and network share Upload of images or video clips: FTP, SFTP, HTTP, HTTPS, network share and email Pre- and post-alarm video or image buffering for recording or upload Notification: email, HTTP, HTTPS, TCP and SNMP trap PTZ: PTZ preset, start/stop guard tour Overlay text, external output activation, play audio clip, day/night mode	
Data streaming	Event data	
Built-in installation aids	Focus assistant, pixel counter, remote back focus	
General		
Casing	Metal (zinc) Color: White NCS S 1002-B	
Sustainability	PVC free	
Memory	512 MB RAM, 256 MB Flash	
Power	8–28 V DC, max 7.3 W, typical 4.2 W Power over Ethernet (PoE) IEEE 802.3af/802.3at Type 1 Class 3, max 6.8 W, typical 3.6 W	
Connectors	RJ45 10BASE-T/100BASE-TX PoE I/O: 4-pin 2.5 mm terminal block for two configurable inputs/outputs RS485/RS422, 2 pcs, 2 pcs, full duplex, terminal block DC input, terminal block, 3.5 mm mic/line in, 3.5 mm line out P-Iris connector (compatible with DC-iris)	
Storage	Support for microSD/microSDHC/microSDXC card Support for SD card encryption Support for recording to network-attached storage (NAS) For SD card and NAS recommendations see www.axis.com	
Operating conditions	0 °C to 55 °C (32 °F to 131 °F) Humidity 10-85% RH (non-condensing)	
Storage conditions	-40 °C to 65 °C (-40 °F to 149 °F)	
Approvals	EMC EN 55022 Class B, EN 61000-3-2, EN 61000-3-3, EN 55024, EN 61000-6-1, EN 61000-6-2, FCC Part 15 Subpart B Class B with shielded cable (STP), FCC Part 15 Subpart B Class A with unshielded cable (UTP), ICES-003 Class B, VCCI Class B, RCM AS/NZS CISPR 22 Class B, KCC KN32 Class B, KN35 Safety IEC/EN/UL 60950-1	
Dimensions	205 x 78 x 46 mm (8.1 x 3.1 x 1.8 in)	
Weight	630 g (1.4 lb)	
Included accessories	Connector kit, Installation Guide, Windows decoder 1-user license, Stand	
Optional accessories	Axis mounts, Axis lenses, Axis midspans For more accessories, see www.axis.com	
Video management software	AXIS Companion, AXIS Camera Station, Video management software from Axis' Application Development Partners available on www.axis.com/vms	
Languages	English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Traditional Chinese	
Warranty	Axis 3-year warranty and AXIS Extended Warranty option, see www.axis.com/warranty	
a. This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (http://www.openssl.org/), and cryptographic software written by Eric Young (eay@cryptsoft.com).		

Environmental responsibility:

www.axis.com/environmental-responsibility

