




M6 SPLIT LOCK WASHER (1)



M6-32 MACHINE SCREW NUT



M6 EXTERNAL TOOTH LOCK WASHER (1)



#10 AWG JUMPER WIRE ASSEMBLY (1)  
PNF10-14R (2)  
#10 AWG WIRE- GREEN & YELLOW STRIPED INSULATED (8.00" [ 203.20 ])

- NOTES:
- 1. PANDUIT PART NO: PGKE
  - 2. WEIGHT: .035 LB/ea  
15.95 g/ea
  - 3. DIMENSIONS IN PARENTHESES ARE IN METRIC.

										CAD FILENAME/LAYERS		C41449_00	
										PANDUIT CORP. TINLEY PARK, ILLINOIS PGKE GROUNDING KIT CUSTOMER DRAWING			
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010(.3) (.XX) ± .03(.8) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
										DRAWN BY KLFU	MAT'L:  SEE NOTES	SCALE NONE	
00	9/04	KLFU		RELEASED						DATE 9/04		DRAWING NO.	
REV	DATE	BY	CHK	DESCRIPTION		ECN	CHK	CUST	SUP	CHECKED BY		C41449	
												A	
												SIZE	