




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
HA0B1E0CA1081	9 lb (4.1 kg)

NOTES:

- IDENTIFICATION: 1RU HORIZONTAL, MIXED (10) C-13 & (2) C-19, AUTO-TRANSFER SWITCH
208V / 20A / SINGLE-PHASE POU
PART NO. HA0B1E0CA1081 COLOR BLACK
- ACCESSORY COMPONENTS:
(4) #10-32 x 1/2" MOUNTING SCREWS
(4) #12-24 x 1/2" MOUNTING SCREWS
- HEXAGONS ARE FOR COMMUNICATION PURPOSES.
- AUTO-TRANSFER SWITCH UNITS WILL AUTOMATICALLY SWITCH FROM THE PRIMARY TO THE SECONDARY POWER SOURCE IF THE PRIMARY POWER SOURCE FAILS. ONCE THE PRIMARY POWER SOURCE BECOMES AVAILABLE AGAIN, THE UNIT WILL AUTO-SWITCH BACK TO THE PRIMARY POWER SOURCE.
- AUTO SWITCHING RELAY:
-SWITCHING TYPE - DPDT RELAY
-UL RELAY CONTACT RATING - 35 AMPS AT 277 VAC
-EXPECTED LIFE AT RATED LOAD - 100,000 OPERATIONS
-OPERATE TIME - <25 MILLISECONDS
-RELEASE TIME - <25 MILLISECONDS
-PICK UP - 85% OR LESS OF NOMINAL
-POWER FEEDS A AND B MUST BE PHASE SYNCHRONIZED
- UL & c-UL LISTED 60950.
- RoHS COMPLIANT.
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
- MAXIMUM AVAILABLE INPUT POWER = 4.2 KW
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.



PLUG
20 AMP, 250V, SINGLE-PHASE
STRAIGHT BLADE
NEMA 6-20P

EIGHT (8)
RECEPTACLES
15 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13

TWO (2)
RECEPTACLES
20 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
00B	5-21-12	MRWA	KRKE	A. ROTATED OUTLETS	09V098XO				
00A	5-11-12	MRWA	KRKE	RELEASED TO PRODUCTION	09V098XO				

MODEL FILENAME	09V098XO/00.PRT	
CAD FILENAME/LAYERS	09V098XO_DC/00B.PRT	
PANDUIT CORP TINLEY PARK, ILLINOIS		
1RU HORIZONTAL, MIXED (8) C-13 & (2) C-19, AUTO-TRANSFER SWITCH POWER OUTLET UNIT CUSTOMER DRAWING		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION
INCHES	[METRIC - MILLIMETER]	ANGLE
X.X	± 0.03	X
X.XX	± 0.015	X.X
X.XXX	± 0.005	X.XX
DRAWN BY	MAT'L:	SCALE
MRWA		NONE
DATE		DRAWING NO.
5-11-12		09V098XO
CHK'D		DWG
KRKE		B
		SIZE