


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



TELESCOPING
DUCT ASSEMBLY

PANDUIT PART NO.

WEIGHT

NSVED0711632BL (BLACK)

39.1 LBS/EACH

NSVED0711632WH (WHITE)


17.7 Kg/EACH

NOTES:

1. VISIT OUR ONLINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. DIMENSIONS IN PARENTHESES ARE METRIC [mm].
3. PARTS SUPPLIED:
 1 - TELESCOPING DUCT ASSEMBLY
 1 - HARDWARE KIT
 1 - SEALING FOAM KIT
 1 - INSTRUCTION SHEET

A

A

										TITLE				
										NSVED0711632				
										700mm 16"-32" VERTICAL EXHAUST DUCT				
										CUSTOMER DRAWING				
										ITEM REVISION NAME		11V269AJ/00.PRT		
										DATASET FILE NAME		11V269AJ_DC/00A.PRT		
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				MATERIAL:
										.x : .06 [1.5] .xxx : .015 [.4] .xx : .03 [.8] ANGLES : 5°				SEE NOTES
										 THIRD ANGLE PROJECTION				DRAWING NUMBER:
00A	03/28/12	PJST			RELEASED TO PRODUCTION				11V269AJ-DC					11V269AJ
REV	DATE	BY	CHK	APR	DESCRIPTION			ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 2	SIZE
									ERK	1/26/12		NONE		A


2

1


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FRONT VIEW
(EXTENDED)2.5 (64)
INCREMENTAL
COARSE ADJUSTMENT
(12 ADJUSTMENT LEVELS)FRONT VIEW
(COLLAPSED)

SIDE VIEW

							TITLE NSVED0711632 700mm 16"-32" VERTICAL EXHAUST DUCT CUSTOMER DRAWING				
							ITEM REVISION NAME 11V269AJ/00.PRT				
							DATASET FILE NAME 11V269AJ_DC/00A.PRT				
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x ± .06 (1.5) .xxx ± .015 (.4) .xx ± .03 (.8) ANGLES ± 5°  THIRD ANGLE PROJECTION		MATERIAL: SEE NOTES		
00A	03/28/12	PJST			SEE SHEET 1 OF 2 FOR REVISIONS	11V269AJ-DC			DRAWING NUMBER: 11V269AJ		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY ERK	DATE 1/26/12	CHK SCALE NONE	SHT 2 OF 2	SIZE A

2

1