



DS-2CE15C2N-IR
720 TVL Picadis Outdoor IR Bullet Camera



Key Features

- 1/3" Picadis
- 1.3MP Sensor: 1280 (H) x 960 (V) Effective Pixels
- 720 TVL Horizontal Resolution
- True Day/Night
- 2.8 mm, 3.6 mm, 6 mm Fixed Lens, 0.1 Lux, f/1.2
- 20 Meters IR Range
- Smart IR, High Dynamic Range
- Superior Video Image Output and Ultra Low Light Illumination
- Wide Operating Temperature Range
- IP66 Weatherproof

Dimensions



Order Model

DS-2CE15C2N-IR

	DS-2CE15C2N-IR
Camera	
Image Sensor	1/3" Picadis
Effective Pixels	1280 × 960
Min. Illumination	0.1 lux @ (f/1.2, AGC on), 0 lux with IR
Shutter speed	1/30 s to 1/30,000 s
Lens	3.6 mm (2.8 mm, 6 mm optional)
	Angle of view: 71.4° (3.6 mm)
Lens Mount	M12
Angle Adjustment	Pan: 0° to 360°, tilt: 0° to 90°, rotation: 0° to 360°
Day/Night	IR cut filter with auto switch
Horizontal Resolution	720 TVL
Synchronization	Internal synchronization
Video Output	1 Vp-p composite output (75 Ω/BNC)
S/N Ratio	More than 62 dB
General	
Working Temperature/Humidity	-40° C to 60° C (-40° F to 140° F) Humidity 90% or less (non-condensing)
Power Supply	12 VDC
Power Consumption	Maximum 1.5 W (maximum 4.5 W with IR cut filter on)
Ingress Protection	IP66
IR Range	20 meters
Dimensions	Φ70 mm × 149.5 mm (Φ2.76" × 5.89")
Weight	360 g (0.79 lbs)