



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

BANDING PART NUMBER	COIL BAND WIDTH ±.010" [0.25]	MAT'L. TYPE	MAT'L. COATING	REQ'D. BANDING HEAD PART NUMBER	MAT'L LENGTH	MAT'L. THICKNESS ±.001" [0.03]	MAT'L. EDGES
MBS-TLR	.173 [4.39]	304	-----	MTHS-C	250.0' [76.2m]	.010" [.25]	NOTE 5
MBH-TLR	.312 [7.92]	304	-----	MTHH-C	250.0' [76.2m]	.010" [.25]	NOTE 5
MBS-TLR316	.173 [4.39]	316	-----	MTHS-C316	250.0' [76.2m]	.010" [.25]	NOTE 5
MBH-TLR316	.312 [7.92]	316	-----	MTHH-C316	250.0' [76.2m]	.010" [.25]	NOTE 5
MBCH-QR316	.312" [7.93]	316	POLYESTER	MTHCH-C316	82.5' [25.0m]	.010" [.25]	NOTE 6



NOTES :

1. INSTALLATION TOOLS:
PPTMT,GS4MT,ST2MT,HTMT & ST3MT.
2. UNLESS OTHERWISE SPECIFIED,
DIMS IN [] ARE IN mm
3. SEE TABLE FOR COMPATIBLE
BANDING HEAD PART NUMBERS.
4. TOLERANCES UNLESS OTHERWISE SPECIFIED:
 .X ± .13(3.30)
5. FULLY ROUNDED EDGES.
6. FULLY COATED MATERIAL.
COATING THICKNESS:
 .003"/.007" [.08/.18] PER SIDE

							TITLE STAINLESS STEEL METAL BANDING CONTINUOUS						
							CUSTOMER DRAWING						
							ITEM REVISION NAME N41194BS/03						
							DATASET FILE NAME N41194BS_DC/03A						
03A	4/13	JAMB	MIM	RGR0	UPDATE DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO	SSECN01047	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °  THIRD ANGLE PROJECTION						
02A	5/05	JAMB	EJD	SKB	A BANDING HEAD PART NUMBER MTHCH-C316 WAS PART NUMBER MTHCHD-C316	12678							
01	11/04	JAMB	EJD	JJB	ADDED PART NO'S MBCH-QR316 TO TABLE	12175							
00	10/04	JAMB	EJD	JJB	DRAWING RELEASED	12064							
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY JAMB	DATE 10/04	CHK EJD	SCALE NONE	DRAWING NUMBER: N41194BS_DC		SIZE A