


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NUMBER	MATERIAL	PACKAGE QTY
MMP350-C	304 SS	100
MMP350-C316	316 SS	100
MMP350-M	304 SS	1000
MMP350-M316	316 SS	1000




SECTION A-A
SCALE 8:1

NOTES:

- DIMENSIONS IN BRACKETS () ARE METRIC.
- CUSTOM PERMANENT MARKING AVAILABLE. CONSULT FACTORY.
- USE WITH STANDARD SERIES CROSS SECTION MLT'S.
- TOLERANCES (UNLESS OTHERWISE SPECIFIED)
 $.xxx = \pm .020$ (.51)
 $.xx = \pm .03$ (.8)

06A	12/12	JAMB	MIM	RGRO	UPDATE DRAWING TO NEW PANDUIT GLOBAL TITLE BLOCK WITH PANDUIT LOGO	SSECN01031
05A	12/12	MIM	RGRO	---	1. ADDED HOLE SPACING DIM 3.00 [76.20] 2. ADDED HOLE LOCATION DIM .25 [6.35] 3. ADD HOLE SPACING DIM .375 +/- .030 [9.525 +/- .76] 4. ADDED HOLE LOCATION DIM .19 [4.79]	-----
04A	08/08	JAMB	SKB	---	ORIG CAD FILE SPEC WAS S41044_04.REMOVED NOTE 5. ADDED PACKAGE QTY TO TABLE. ADDED PART NO'S FOR BULK QTY 1000 MARKER PLATES	-----
04	01/01	KMD	JD	---	ADDED NOTE 5. CAD FILE SPEC WAS N41044_PCD_03	07257
03	11/98	JKD	SM	---	ADDED NOTE 4. MAT'L WAS 302/304 FOR MMP350	05241
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE					
STANDARD METAL MARKER PLATE					
CUSTOMER DRAWING					
ITEM REVISION NAME					
N41044BS/06					
DATASET FILE NAME			MATERIAL:		
N41044BS_DC/06A					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			SEE NOTES		
.x ± .1 [2.54]			.xxx ± .005 [.127]		
.xx ± .01 [.25]			ANGLES ± 5 °		
			THIRD ANGLE PROJECTION		
DRAWN BY			DRAWING NUMBER:		
SAM			N41044BS_DC		
DATE			SIZE		
02/04/91			A		
CHK					
LM					
SCALE					
NTS			SHT 1 OF 1		