



760175919 | CPP-FCM-KIT
Fiber Cable Management Kit

Product Classification

Portfolio	CommScope®
Product Type	Cable management hardware
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Depth	195.58 mm 7.70 in
Height	38.10 mm 1.50 in
Weight	0.09 kg 0.20 lb
Width	436.88 mm 17.20 in

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Package Quantity	1
------------------	---

Mechanical Specifications

Material Type	Stainless steel
---------------	-----------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	
ISO 9001:2008	