


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


NOTES:

1. SEE SHEETS 2, 3 & 4 FOR PRODUCT DESCRIPTIONS AND TECHNICAL SPECIFICATIONS.
2. SEE CURRENT CATALOG FOR PATCH CORD LENGTHS AND PACKAGE QUANTITIES.
3. FOR LENGTHS OTHER THAN THOSE LISTED IN CATALOG, CONTACT YOUR PANDUIT SALES PERSON.
4. TESTED TO EIA/TIA 568-B.3.
5. PATCH CORD ROUTING CONFIGURATION A TO B.
6. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.



DUPLEXED LC CONNECTORS
(PRINTED CABLE SIDE B)

DUPLEXED LC CONNECTORS
(PRINTED CABLE SIDE A)



										FIBER OPTIC PATCH CORD DUPLEX LC TO LC CONFIGURATION CUSTOMER DRAWING			
										 PANDUIT ™ CORP. TINLEY PARK, ILL 60477			
										ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED.		DRAWING FILENAME M02779BC_DC/01A	
										DIMENSIONAL TOLERANCES ARE: (.X) ±.010 (0.3) (.XX) ±.03 (0.8) ANGLES		SCALE NONE	
										THIRD ANGLE PROJECTION		PART NO. SEE SHEETS 2, 3 & 4	
										DRAWN BY MC		REVIEW DRAWING NUMBERS	
										DATE 04-27-07		DRAWING NO. 02779-11	
										CHK'D RAF		SIZE A	
01	09-09-09	EFK		RELEASED TO PRODUCTION	02779-11								
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH				

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

DUPLEX LC TO LC FIBER OPTIC PATCH CORD							
PANDUIT PART NO.	CABLE				LC CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	MIN. RL	BOOT COLOR
F5E10-10M*Y	RISER (OFNR)	50/125um	DUPLEX 1.6mm ZIPCORD	ORANGE	0.25dB	20dB	BLACK
F6E10-10M*Y		62.5/125um					ELECTRIC IVORY
FXE10-10M*Y		10GbE OM3		AQUA	0.25dB	26dB	AQUA
FXOE10-10M*		OPTIMIZED 10GbE OM3			0.15dB	26dB	
FZE10-10M*		10GbE OM4		AQUA	0.25dB	26dB	AQUA
FZOE10-10M*		OPTIMIZED 10GbE OM4			0.15dB	26dB	
F9E10-10M*Y		9/125um OS1		YELLOW	0.35dB	55dB	BLUE

* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET



REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
01	09-09-09	EFK		RELEASED TO PRODUCTION	02779-11				

FIBER OPTIC PATCH CORD DUPLEX LC TO LC CONFIGURATION CUSTOMER DRAWING									
				PANDUIT ™ CORP. TINLEY PARK, ILL 60477					
 THIRD ANGLE PROJECTION				ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.010 (.3) ±.008 ANGLES				DRAWING FILENAME M02779BC_DC/01A	
				DRAWN BY MC DATE 04-27-07 CHK'D RAF				SCALE NONE	
				REVIEW DRAWING NUMBERS				PART NO. SEE SHEETS 2, 3 & 4	
								DRAWING NO. 02779-11 SHEET 2 OF 4	
								SIZE A	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

DUPLEX LC TO LC FIBER OPTIC PATCH CORD							
PANDUIT PART NO.	CABLE				LC CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	MIN. RL	BOOT COLOR
F5LE10-10M*	LOW SMOKE ZERO HALOGEN (LSZH) IEC	50/125um OM2	DUPLEX 1.6mm ZIPCORD	ORANGE	0.25dB	20dB	BLACK
F6LE10-10M*		62.5/125um OM1					ELECTRIC IVORY
FXLE10-10M*		10GbE OM3		AQUA	0.25dB	26dB	AQUA
FXOLE10-10M*		OPTIMIZED 10GbE OM3			0.15dB	26dB	
FZLE10-10M*		10GbE OM4		AQUA	0.25dB	26dB	AQUA
FZOLE10-10M*		OPTIMIZED 10GbE OM4			0.15dB	26dB	
F9LE10-10M*		9/125um OS1		YELLOW	0.35dB	55dB	BLUE

* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

										FIBER OPTIC PATCH CORD DUPLEX LC TO LC CONFIGURATION CUSTOMER DRAWING					
										 PANDUIT ™ CORP. TINLEY PARK, ILL 60477					
										 THIRD ANGLE PROJECTION		ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.010 (.3) ±.008 ANGLES		DRAWING FILENAME M02779BC_DC/01A	
										DRAWN BY MC		REVIEW DRAWING NUMBERS		PART NO. SEE SHEETS 2, 3 & 4	
										DATE 04-27-07		DRAWING NO. 02779-11		SIZE A	
01	09-09-09	EFK		RELEASED TO PRODUCTION	02779-11					CHK'D RAF	SHEET 4 OF 4				
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH						