


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:
1. IDENTIFICATION: VERTICAL, MIXED (24) C-13 & (6) C-19 NETWORKED 230/400V / 32A / THREE-PHASE WYE POU



DETAIL A (SCALE 4X)

PANDUIT P/N	WEIGHT
QZ1D2P6BM30P1	17 lb (7.7 kg)

PART NO.	COLOR
QZ1D2P6BM30P1	BLACK

2. ACCESSORY COMPONENTS:
 (4) #10-32 x 1/2" MOUNTING SCREWS
 (4) #12-24 x 1/2" MOUNTING SCREWS
 (2) #10-32 LOCKING COLLAR SCREWS
 (2) L-BRACKETS

3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).


4. CURRENT METER - RED, 4-DIGIT LED DISPLAY PROVIDES TRUE RMS CURRENT THAT CONTINUOUSLY SCROLLS THROUGH THE THREE DIFFERENT MEASURED CIRCUITS. METER DISPLAYS CIRCUIT NAME FOLLOWED BY THE MEASURED CURRENT (E.G. CR-1 REPRESENTS PHASE 1). BREAKER/PHASE (X,Y,Z) LEVEL MONITORING CAN ALSO BE ACCESSED REMOTELY VIA ETHERNET CONNECTION.

5. UNIT COMPLIES WITH IEC 60950-1, EN55022, EN55024, AND IS CE MARKED.


6. RoHS COMPLIANT.

7. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.

8. MAXIMUM AVAILABLE POWER = 22.1 KW




TOOLLESS MOUNTING BUTTON LOCATION




NETWORKED CURRENT METER (SEE DETAIL A)


16 AMP, SINGLE POLE UL LISTED ELECTRO MECHANICAL SWITCH/BREAKER 6 PLACES




3 METER INLET POWER CORD



PLUG
32 AMP, 230/400V x 3~ WYE
4P/5W
IEC 60309, SPLASHPROOF



TWENTY-FOUR (24)
RECEPTACLES
15 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13



SIX (6)
RECEPTACLES
20 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
00A	2-7-11	MAV	KRKE	RELEASED TO PRODUCTION	09V098VB				

MODEL FILENAME	09V098VB/00.PRT
CAD FILENAME/LAYERS	09V098VB_DC/00A.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS
 VERTICAL, MIXED (24) C-13 & (6) C-19, NETWORKED
 POWER OUTLET UNIT (QZ1D2P6BM30P1)
 CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES: X.X +/- 0.03, X.XX +/- 0.015, X.XXX +/- 0.005 [METRIC - MILLIMETER]: X +/- 0.8, X.X +/- 0.4, X.XX +/- 0.13		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
DRAWN BY: MAV	MAT'L:	SCALE: NONE	
DATE: 2-7-11	CHK'D: KRKE	DRAWING NO.: 09V098VB	DWG SIZE: B