





CONNECTOR SPECIFICATION:

VOLTAGE RATING		250 VAC/VDC	
AMPERAGE RATING		max. 4 AMPS	
PROTECTION		IP67	
OPERATING TEMPERATURE		-20°C TO 105°C	
UL CERTIFICATIONS		UL RECOGNIZED, FILE NO. E152210	
ASSEMBLY IS		RoHS COMPLIANT	
COMPONENT	MATERIAL	FINISH	
LABEL	MYLAR	BLACK/YELLOW	
COUPLER	BRASS	NICKEL PLATED	
PIN CONTACT	COPPER ALLOY	GOLD OVER NICKEL	
INSERT	NYLON	BLACK	
OVERMOLD	PUR	YELLOW	
CABLE- 22/3-5 (COPPER STRANDING) 3/4/5 CONDUCT. 300V	JACKET: PVC	JACKET: YELLOW	

MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH
1200661137	883031A09M010	1.0M +55.6 -0 [3.28' +2.19" -0]
1200661389	885031A09M010	1.0M +55.6 -0 [3.28' +2.19" -0]
1200661262	884031A09M010	1.0M +55.6 -0 [3.28' +2.19" -0]
1200661280	884031A09M100	10.0M +55.6 -0 [32.8' +2.19" -0]

UPDATED FOR PART MATRIX EC NO: IPG2014-0988 DRWN: GGUSTAFS CHKD: TWOLDEGE APPR: BWOODMAN 2010/01/29			QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION	
							IN/MM		NTS	INCH		
				 = 0  = 0		mm	INCH	DRAWN BY	DATE	MICRO-CHANGE CORDSET 3/4/5 POLE FE 90 /MA STR 22/AWG YELLOW PVC CABLE		
					4 PLACES	±.---	±---	LSTEMMLE	2010/01/25			
					3 PLACES	±.---	±.005	CHECKED BY	DATE			
2 PLACES	±.13	±.010	RE		2010/01/26							
A			REV	DESCRIPTION	1 PLACE	±.25	±.020	APPROVED BY	DATE	 MOLEX INCORPORATED		
					ANGULAR ± .5 °			NSTAUDIG	2010/01/29			
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.		DOCUMENT NO.		SHEET NO.
								SEE CHART		SD-120066-013		1 OF 1
								SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			