

# Mini O 1080p

1080p Wi-Fi Indoor Cloud Camera



## Introduction

EZVIZ products have been designed for your entertainment, communication and security. When you install the EZVIZ APP on your smartphone or tablet, EZVIZ devices will connect to the cloud via their QR code. With EZVIZ you can talk to your loved ones, watch your child's progress when you are away, keep an eye on your home and interact with your pets.

## Main Features



Full HD 1080p



MicroSD Card Slot (Up to 128GB)



Wi-Fi Certified 2.4GHz



Two-Way Audio, built-in Microphone and Speaker



Night Vision



Secure Cloud Recording\*

\*Subscription is required for cloud recording.

## Dimensions



# Specifications

Model	Pro-MINOPLS
	1080p Wi-Fi Indoor Cloud Camera
<b>Camera</b>	
Image sensor	1/2.7"2MP Progressive Scan CMOS
Minimum Illumination	0.02Lux @(F2.0,AGC ON), 0 Lux with IR
Shutter	1/30s to 1/100,000s
Lens	2.8mm @ F2.0 Horizontal View Angle: 115°,Diagonal View Angle: 135°
Lens Mount	M12
Day & Night	IR cut filter
DNR	3D DNR
IR Range	Up to 25 feet (7.5m)
WDR	Digital WDR
Audio	Built-in Microphone and Speaker
<b>Compression</b>	
Video Compression	H.264 Main Profile
Video Bit Rate	Hi-Def, Standard, and Basic . Adaptive bit rate.
Audio Bit Rate	Adaptive bit rate
<b>Image</b>	
Max. Resolution	1920 x 1080
Frame Rate	15fps (1920 x 1080)
<b>Network</b>	
Storage	Support microSD card (≤ 128 GB)
Smart Alarm	Smart motion detection
One-key configuration	SmartConfig (Wi-Fi one-key configuration)
Interface Protocol	EZVIZ Cloud Proprietary Protocol
General Function	Dual-stream, Mirror image
<b>Wireless parameters</b>	
Standard	IEEE802.11b, 802.11g, 802.11n
Frequency Range	2.4 GHz to 2.4835 GHz
Channel Bandwidth	Support 20MHz
Security	64/128-bit WEP, WPA/WPA2, WPA-PSK/WPA2-PSK
Transmission Rate	802.11b: 11Mbps, 802.11g: 54Mbps, 802.11n: 150Mbps
<b>General</b>	
Operating Conditions	14 °F to 113 °F (-10°C ~ 45°C), Humidity 95% or less (non-condensing)
Power Consumption	5 VDC±10% , 3W maximum
Dimensions (inch)	4.33"*2.28"*1.50"(110mm*58mm*38mm )
Weight	0.26 lb (120 g)