



760051151 | 1100GS5-24

**GigaSPEED X10D® 1100GS5 Category 6A U/UTP Patch Panel, 24 port**

## **OBSOLETE**

**This product was discontinued on: July 1, 2011**

### **Replaced By**

760152587 SYSTIMAX 360™ GigaSPEED X10D® 1100GS6 Evolve Category 6A U/UTP Patch Panel, 24  
360-IPR-1100-E-GS6-1U-24 port

## **Product Classification**

Portfolio	SYSTIMAX®
Brand	GigaSPEED X10D®
Product Type	Copper patch panel
Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America

## **Dimensions**

Depth	40.64 mm   1.60 in
Diameter Over Dielectric, maximum	1.168 mm   0.046 in
Diameter Over Dielectric, minimum	0.762 mm   0.030 in
Height	44.45 mm   1.75 in
Width	482.60 mm   19.00 in

## **Electrical Specifications**

ANSI/TIA Category	6A
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

## **Environmental Specifications**

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

## **General Specifications**

Intelligence Type	Passive
Total Ports, quantity	24
Cable Type	U/UTP (unshielded)
Brand	GigaSPEED X10D®   SYSTIMAX®
Color	Black

760051151 | 1100GS5-24

Modules, quantity	4
Package Quantity	1
Rack Type	EIA 19 in
Rack Units	1

## Mechanical Specifications

Panel Style	Straight
Conductor Gauge, solid	22 AWG   24 AWG
Conductor Gauge, stranded	22 AWG   24 AWG
Conductor Type	Solid   Stranded
Material Type	High-impact, flame retardant, thermoplastic   Powder-coated steel
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Insertion Life, test plug	IEC 60603-7 compliant plug
Plug Retention Force, minimum	30 lbf   133 N
Rear Termination Contact Plating	Nickel
Rear Termination Type	IDC
Wiring	T568A   T568B

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system