



CPC5513-07 | VP-P8GS-X3-RD

**GigaSPEED XL® VisiPatch® to VisiPatch® 4-pair Patch Cord Crossover, Red Jacket**

## Product Classification

Portfolio	SYSTIMAX®
Brand	GigaSPEED XL®   VisiPatch®
Product Type	Twisted pair patch cord
Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

Cord Length, maximum	30 m   100 ft
Cord Length, minimum	1 m   1 ft

## Electrical Specifications

ANSI/TIA Category	6
dc Resistance, maximum	0.30 ohm

## Environmental Specifications

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL   ETL

## General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	VisiPatch®
Interface, connector B	VisiPatch®
Jacket Color	Red
Brand	GigaSPEED XL®   SYSTIMAX®   VisiPatch®
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package Quantity	1
Pairs, quantity	4

## Mechanical Specifications

Conductor Type	Stranded
----------------	----------

CPC5513-07 | VPP8GS-X3-RD

Material Type                      Copper alloy | Polycarbonate  
Outlet/Module Contact Plating    Precious metals  
Plug Insertion Life, minimum    200 times  
Plug Retention Force, minimum   44 N | 10 lbf  
Wiring                                VisiPatch® crossover

## Wiring Diagram

	Connector A	Connector B
Position 1	Lt. Blue	Lt. Brown
Position 2	Blue	Brown
Position 3	White/Orange	Lt. Green
Position 4	Orange	Green
Position 5	Lt. Green	White/Orange
Position 6	Green	Orange
Position 7	Lt. Brown	Lt. Blue
Position 8	Brown	Blue

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



## Included Products

860018639 | 1074E RD 4/24 RVAR (Product Component—not orderable) — GigaSPEED XL® 1074E Category 6 U/UTP Cable, non-plenum, red jacket, 4 pair count, variable length, reel