


PART NUMBER	MATERIAL	"A" HEIGHT +/- .062	IMPRINT AREA "B" +/- .062	VERTICAL REPEAT "C" +/- .062	LABELS PER ROW	STANDARD PKG. QTY.
S200X150TAT	GMT1	1.50 [12.7]	0.50 [12.7]	1.75 [44.5]	2	5000
S200X250TAT		2.50 [63.5]	1.00 [25.4]	2.75 [69.8]		1000
S200X150VATY	GMV16 OR GMV17	1.50 [12.7]	0.50 [12.7]	1.75 [44.5]		5000
S200X225VATY		2.25 [57.2]	0.75 [19.1]	2.50 [63.5]		1000
S200X250VATY		2.50 [63.5]	1.00 [25.4]	2.75 [69.8]		
S200X400VATY		4.00 [101.6]		4.25 [108.0]		
S200X650VATY		6.50 [165.1]	1.50 [38.1] +/- .10	6.75 [171.5]		

NOTES:

1. MILLIMETERS ARE IN [].



CAD FILENAME/LAYERS

I00472BY_DC_C10468/08H

7	10/25/11	RVU		"GMV16 OR GMV17" WAS "GMV".	6548	R					PANDUIT CORP. TINLEY PARK, ILLINOIS CUSTOMER DRAWING OPTIMUM SELF-LAM. S200X***VATY THERMAL TRANSFER PRINTABLE LABELS UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (.XXX) ± .025 (.XX) ± .062 ANGLES ± UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION. SCALE NTS DRAWING NO. C10468 DWG A SIZE	
6	12/10/09	RVU	MSAD	UPDATE ON ALL STANDARD TOLERANCES. ADD +/- .10 TO 1.50.	5925	R						
5	3/5/09	RVU		5000 WAS 1000. +/- .062 UPDATE. This change was originally initiated and approved under ECN 5371 but the drawing change was not properly implemented.	5698	R						
4				VOID								
3	1-6-09	RVU		1.50 +/- .10 WAS 1.00 +/- .031. CHANGE SIZE B TO A. .12, .062, .020 WAS .030, .015, .010. REMOVE NOTE 2. REMOVE ALL VAT PARTS. ADDED NEW P/N. S200X150TAT, S200X250TAT, AND S200X250VATY. S200X***VATY, GMV16 WAS GMV.	5633	R					SEE TABLE	
2	5/30/07	RVU			5021	R						
1	1-8-07	RVU		REVISED TOLERANCES.	4830	R						
0	9-1-06	RVU		DRAWING RELEASED.	4671	R						
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP		CHK'D		