



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	PACKAGED	WEIGHT
MPS588-C	100/BAG	.55 LB/100 PCS (250 g/100 PCS)

NOTES:

1. PART NUMBER: SEE TABLE.
2. MATERIAL: HOUSING - THERMOPLASTIC UL94V-0 RATED;
TERMINAL - PHOSPHOR BRONZE ELECTRO-POLISHED AND
PLATED WITH .000050" MIN. GOLD IN MATING AREA, GOLD
FLASH OVER REMAINDER, .000100" MIN. NICKEL UNDERPLATE.
SHIELD - CATRIDGE BRASS WITH .000100" MIN. OF NICKEL.
3. PLUG ACCEPTS 4-PAIR CABLE .210"-.250" DIAMETER CABLE
WITH 24-26 AWG STRANDED OR SOLID CONDUCTOR WITH
MAXIMUM INSULATOR DIAMETER OF .040"
4. ALL DIMENSIONS MAXIMUM UNLESS OTHERWISE SPECIFIED.
5. TERMINATED CONTACT HEIGHT: .237±.005".




PART NUMBER		PRODUCT SPEC/PKG SPEC	
N/A		N/A	
I.I. NUMBER		WORK INSTRUCTION	
N/A		N/A	
TITLE			
SHIELDED PAN-PLUG HIGH PERFORMANCE MODULAR PLUG			
CUSTOMER DRAWING			
ITEM REVISION NAME			
D35123AN/03			
DATASET FILE NAME		MATERIAL:	
D35123AN_DC19/03A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		DRAWING NUMBER:	
.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °			
		35123-19	
THIRD ANGLE PROJECTION			
DRAWN BY	DATE	CHK	SCALE
LZ	11-14-00	RAV	1 TO 1
SHT 1 OF 1			SIZE
			A


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	PACKAGED	WEIGHT
MPS588-C	100/BAG	.55 LB/100 PCS (250 g/100 PCS)

NOTES:

1. PART NUMBER: SEE TABLE.
2. MATERIAL: HOUSING - THERMOPLASTIC UL94V-0 RATED;
TERMINAL - PHOSPHOR BRONZE ELECTRO-POLISHED AND
PLATED WITH .000050" MIN. GOLD IN MATING AREA, GOLD
FLASH OVER REMAINDER, .000100" MIN. NICKEL UNDERPLATE.
SHIELD - CATRIDGE BRASS WITH .000100" MIN. OF NICKEL.
3. PLUG ACCEPTS 4-PAIR CABLE .210"-.250" DIAMETER CABLE
WITH 24-26 AWG STRANDED OR SOLID CONDUCTOR WITH
MAXIMUM INSULATOR DIAMETER OF .040"
4. ALL DIMENSIONS MAXIMUM UNLESS OTHERWISE SPECIFIED.
5. TERMINATED CONTACT HEIGHT: .237±.005".



PART NUMBER		PRODUCT SPEC/PKG SPEC	
N/A		N/A	
I.I. NUMBER		WORK INSTRUCTION	
N/A		N/A	
TITLE			
SHIELDED PAN-PLUG HIGH PERFORMANCE MODULAR PLUG			
CUSTOMER DRAWING			
ITEM REVISION NAME			
D35123AN/03			
DATASET FILE NAME		MATERIAL:	
D35123AN_DC19/03A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		DRAWING NUMBER:	
.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °			
		35123-19	
THIRD ANGLE PROJECTION			
DRAWN BY	DATE	CHK	SCALE
LZ	11-14-00	RAV	1 TO 1
SHT 1 OF 1			SIZE
			A