

AXIS P5414-E PTZ Dome Network Camera

Intelligent direct drive PTZ dome with HDTV 720p

AXIS P5414-E is an outdoor-ready HDTV 720p PTZ dome with 18x optical zoom. Designed to blend in with a building, AXIS P5414-E mounts directly on the wall with a built-in bracket for ease of installation. When mounted on the corner of a building, it enables 270° pan for wide area coverage. AXIS P5414-E features a direct drive pan/tilt system with no belts or gears, enabling reliable, low-maintenance mechanics. The sunshield can be easily removed and repainted to match the wall color. A hidden junction box supports two-way audio, a memory card slot, four configurable input/output ports, 24 V DC and Power over Ethernet.

- > **Outdoor wall-mount design for easy installation**
- > **Repaintable, integrated sunshield**
- > **Durable, low maintenance mechanics**
- > **HDTV 720p performance and 18x optical zoom**
- > **Two-way audio & input/output ports**



AXIS P5414-E PTZ Dome Network Camera

Models	AXIS P5414-E 50 Hz AXIS P5414-E 60 Hz	PTZ: PTZ preset, start/stop guard tour File upload via FTP, SFTP, HTTP, HTTPS network share and email Notification via email, HTTP, HTTPS and TCP	
Camera			
Image sensor	1/2.8" progressive scan RGB CMOS	Data streaming Event data	
Lens	4.7–84.6 mm, F1.6–2.8 Horizontal field of view: 59°–4° Vertical field of view: 35°–2° Autofocus	Built-in installation aids Pixel counter	
Day and night	Automatically removable infrared-cut filter	General	
Minimum illumination	Color: 0.4 lux at 30 IRE F1.6 B/W: 0.04 lux at 30 IRE F1.6	Casing IP66- and NEMA 4X-rated, IK07 impact-resistance Metal casing (aluminum), clear dome (PC), sunshield (ASA)	
Shutter time	1/28000 s to 2 s	Sustainability PVC free	
Pan/Tilt/Zoom	Pan: ± 135° ^a 0.2°–350°/s Tilt: 0°–90° 0.2°–350°/s Zoom: 18x optical, 12x digital zoom, Total 216x zoom Nadir flip, 100 preset positions, limited guard tour, control queue, focus window, on-screen directional indicator	Memory 256 MB RAM, 128 MB Flash	
Video			
Video compression	H.264 (MPEG-4 Part 10/AVC) Baseline and Main Profiles Motion JPEG	Power Axis PoE+ midspan 1-port: 100–240 V AC, max 37 W IEEE 802.3at Type 2 Class 4 Multi-connector cable: 24 V DC, max 16 W PoE+ midspan and power supply not included.	
Resolutions	1280x720 to 160x90	Connectors RJ45 for 10BASE-T/100BASE-TX PoE Terminal blocks for DC input, 4 configurable alarm inputs/outputs, mic in/line in, line out	
Frame rate	Up to 30/25 fps (60/50 Hz) in all resolutions	Storage Support for microSD/microSDHC/microSDXC card Support for SD card encryption Support for recording to network-attached storage (NAS) For SD card and NAS recommendations see www.axis.com	
Video streaming	Multiple, individually configurable streams in H.264 and Motion JPEG Controllable frame rate and bandwidth VBR/CBR H.264	Operating conditions -20 °C to 50 °C (-4 °F to 122 °F) Humidity 10–100% RH (condensing)	
Image settings	Compression, color, brightness, sharpness, contrast, white balance, exposure control, exposure zones, WDR, backlight compensation, fine tuning of behavior at low light, text and image overlay, 20 individual 3D privacy masks	Storage conditions -40 °C to 65 °C (-40 °F to 149 °F) Humidity 10–80% RH (non-condensing)	
Audio			
Audio streaming	Two-way	Approvals EN 50121-4, IEC 62236-4: 2008, EN 50581, EN 55022 Class B, EN 61000-6-1, EN 61000-6-2, EN 55024, FCC Part 15 Subpart B Class B, ICES-003 Class B, VCCI Class B, C-tick AS/NZS CISPR 22 Class B, KCC KN22 Class B, KN24, IEC/EN/UL 60950-1, IEC/EN/UL 60950-22, IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-6, IEC 60068-2-14, IEC 60068-2-27, IEC 60068-2-30, IEC 60068-2-78, IEC 60529 IP66, NEMA 250 Type 4X, IEC 62262 Class IK07, ISO 4892-2	
Audio compression	AAC-LC 8/16 kHz, G.711 PCM 8 kHz, G.726 ADPCM 8 kHz Configurable bit rate	Dimensions 265 x 169 x 224 mm (10 7/16 x 6 5/8 x 8 13/16 in)	
Audio input/output	External microphone or line input, and line output	Weight 3.5 kg (7.7 lb.)	
Network			
Security	Password protection, IP address filtering, HTTPS ^b encryption, IEEE 802.1X ^b network access control, Digest authentication, User access log, Centralized Certificate Management	Included accessories Installation Guide, AVHS Authentication key, Windows decoder 1-user license AXIS ACI Conduit Adapter 3/4" U-Shape 30 mm Weather Cover	
Supported protocols	IPv4/v6, HTTP, HTTPS ^b , SSL/TLS ^b , QoS Layer 3 DiffServ, FTP, SFTP, CIFS/SMB, SMTP, Bonjour, UPnP TM , SNMP v1/v2c/v3 (MIB-II), DNS, DynDNS, NTP, RTSP, RTP, TCP, UDP, IGMP, RTCP, ICMP, DHCP, ARP, SOCKS, SSH, NTCP	Optional accessories AXIS P54 Smoked Dome AXIS T8133 Midspan 30 W 1-port AXIS T8415 Wireless Installation Tool AXIS T94P01B Corner Bracket AXIS T98A19-VE Surveillance Cabinet For more accessories, see www.axis.com	
System integration			
Application Programming Interface	Open API for software integration, including VAPIX [®] and AXIS Camera Application Platform; specifications at www.axis.com AXIS Video Hosting System (AVHS) with One-Click Connection ONVIF [®] Profile S and ONVIF [®] Profile G, specification at www.onvif.org	Video management software AXIS Companion, AXIS Camera Station, video management software from Axis' Application Development Partners available on www.axis.com/techsup/software	
Analytics	AXIS Video Motion Detection 4, audio detection, advanced gatekeeper Support for AXIS Camera Application Platform enabling installation of third-party applications, see www.axis.com/acap	Languages English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Traditional Chinese	
Event triggers	Detectors: live stream accessed, video motion detection Hardware: network, temperature, fan Input Signal: manual trigger, virtual inputs PTZ: error, moving, preset reached, ready Storage: disruption, recording System: system ready Time: recurrence, use schedule	Warranty Axis 3-year warranty and AXIS Extended Warranty option, see www.axis.com/warranty	
Event actions	Day/night mode, overlay text, video recording to edge storage, pre- and post-alarm video buffering, external output activation, send SNMP trap, play audio clip		

- With corner-mount installations, there is slight visual obstruction from the housing in the upper left/right corner of the image at pan end points.
- This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit. (www.openssl.org), and cryptographic software written by Eric Young (ey@cryptsoft.com).

Environmental responsibility:

www.axis.com/environmental-responsibility