




Technical drawing of a V-shaped structure, likely a roof or a large container. The drawing shows two main sloped sections meeting at a central point. On the left side, there is a vertical dimension line indicating a height of 5.49 and a horizontal dimension line indicating a width of 139.5. The structure features several rectangular openings or compartments along its length. The drawing is a line art representation with no shading.

PANDUIT PART NO.	WEIGHT (APPROX.)
QASP24BL	0.77 lb (348.6 g)

1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS.
2. THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
3. DIMENSIONS IN BRACKETS ARE IN METRIC.
4. PART INCLUDES:
 - 1- METAL STAMPING WITH SLIDE GUIDES
 - 1- SCREW KIT (INCLUDES FOUR #12-24 BONDING SCREWS)
 - 1- SCREW KIT (INCLUDES FOUR M6 BONDING SCREWS)



PART NUMBER		QASP24BL	
TITLE			
QUICKNET ANGLED 24 PORT SHIELDED PATCH PANEL			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02816AD/02	
DATASET FILE NAME		M02816AD_DC19/02A	
<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]</p> <p>.X ± .XXX ± .010 [.3]</p> <p>.XX ± .03 [.8]</p>  <p>THIRD ANGLE PROJECTION</p>		<p>PANDUIT</p> <p>MATERIAL:</p> <p>PANEL: STAINLESS STEEL GUIDES: ABS</p> <p>DRAWING NUMBER:</p> <p>02816-19</p>	
DRAWN BY	DATE	CHK	SCALE
JSP	3/25/14	REFR	NONE
SHT 1 OF 1			SIZE
			A