

AXIS Q6044-S PTZ Dome Network Camera

Pressurized, stainless steel PTZ dome with HDTV 720p and 30x zoom

AXIS Q6044-S is a high-speed surveillance camera in a pressurized, marine-grade stainless steel casing. With endless 360° pan and 30x optical zoom, it provides wide area coverage and detailed surveillance in HDTV 720p resolution. Electronic image stabilization gives more useful video in windy conditions. The stainless steel casing gives the camera high resistance to corrosion, cleaning chemicals and high-pressure steam. The casing can be filled with nitrogen to prevent internal condensation and create a nonflammable environment. The media converter switch allows cameras to be connected in a daisy chain to the network using standard network or fiber optic cables.

- > **Marine-grade stainless steel**
- > **Casing for pressurized nitrogen**
- > **HDTV 720p and 30x optical zoom**
- > **SFP slots for fiber, RJ45 connections**
- > **I/O for alarm in/out**



AXIS Q6044-S PTZ Dome Network Camera

Models	AXIS Q6044-S 60 Hz AXIS Q6044-S 50 Hz	Data streaming	Event data
Camera		Built-in installation aids	Pixel counter
Image sensor	1/3" Progressive scan CCD	General	
Lens	4.4–132 mm, F1.4–4.6 Horizontal angle of view 62.9°–2.2° Vertical angle of view 37°–1.2° Autofocus	Casing	IP6K9K-, IP66-, IP67-, NEMA 4X-, NEMA 6P- and IK10-rated ^b stainless steel casing (V4A, SAE 316L/UNS S31603/EN 1.4432), Nylon clear dome
Day and night	Automatically removable infrared-cut filter	Memory	512 MB RAM, 128 MB Flash Battery backed-up real-time clock
Minimum illumination	Color: 0.2 lux at 30 IRE F1.4 B/W: 0.04 lux at 30 IRE F1.4 Color: 0.3 lux at 50 IRE F1.4 B/W: 0.05 lux at 50 IRE F1.4	Power	12.0–13.2 V DC, min 75 W
Shutter time	1/10000 s to 1/4 s	Connectors	RJ45 10BASE-T/100BASE-TX, IP66-rated multi-connector for DC power, input and output, including 7 m (23 ft) cable
Pan/Tilt/Zoom	Pan: 360° endless, 0.05° – 450°/s Tilt: 220°, 0.05°–450°/s 30x optical zoom and 12x digital zoom, total 360x zoom E-flip, 256 preset positions, Tour recording, Guard tour, Control queue, On-screen directional indicator, Set new pan 0°, Adjustable zoom speed	Storage	Support for SD/SDHC/SDXC card Support for recording to dedicated network-attached storage (NAS) For SD card and NAS recommendations see www.axis.com
Video		Operating conditions	–30 °C to 50 °C (–22 °F to 122 °F) Humidity 10–100% RH (condensing)
Video compression	H.264 (MPEG-4 Part 10/AVC) Baseline and Main Profiles Motion JPEG	Storage conditions	–40 °C to 65 °C (–40 °F to 149 °F)
Resolutions	HDTV 720p 1280x720 to 320x180	Approvals	EN 55022 Class A, EN 61000-3-2, EN 61000-3-3, EN 61000-6-1, EN 61000-6-2, EN 55024, FCC Part 15 Subpart B Class A, ICES-003 Class A, VCCI Class A, C-tick AS/NZS CISPR 22 Class A KCC KN22 Class A, KN24, IEC/EN/UL 60950-1 EN 50121-4, IEC 62236-4, IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-6, IEC 60068-2-14, IEC 60068-2-27, NEMA 250 Type 4X IEC/EN/UL 60950-22, IEC 60068-2-30, IEC 60068-2-60, IEC 60068-2-78 IEC/EN 60529 IP66, IP67, IP6K9K, NEMA 250 Type 6P, MIL-STD 810G 509.5
Frame rate	Up to 30/25 fps (60/50 Hz) in all resolutions	Weight	5.7 kg (12.6 lb)
Video streaming	Multiple, individually configurable streams in H.264 and Motion JPEG Controllable frame rate and bandwidth VBR/MBR H.264	Dimensions	Without sunshield: Ø224 x 256 mm (Ø8.8 x 10.1 in), With sunshield: Ø250 x 256 mm (Ø9.8 x 10.1 in)
Image settings	Wide Dynamic Range (WDR), manual shutter time, compression, color, brightness, sharpness, white balance, exposure control, exposure zones, backlight compensation, fine tuning of behavior at low light, rotation: 0°, 180°, text and image overlay, 32 individual 3D privacy masks, image freeze on PTZ, electronic image stabilization, automatic defog	Included accessories	AXIS T8605 Media Converter Switch, 7 m (23 ft) IP66-rated multi-connector cable Installation Guide, Windows decoder 1-user license
Network		Optional accessories	Power Supply, SFP modules, Wall bracket, AXIS T91C67 Pole Bracket, AXIS T91C61 Wall Mount, AXIS T94S01D Pendant kit (1 1/2" NPT male Thread Adapter), Smoked dome cover, Stainless steel sunshield AXIS T90 Illuminators, AXIS T8310 Video Surveillance Control Board, Installation Display, Multi-user decoder license pack
Security	Password protection, IP address filtering, HTTPS ^a encryption, IEEE 802.1X ^a network access control, Digest authentication, User access log, Centralized Certificate Management	Video management software	AXIS Camera Companion, AXIS Camera Station, Video management software from Axis' Application Development Partners available on www.axis.com/techsup/software
Supported protocols	IPv4/v6, HTTP, HTTPS ^a , SSL/TLS ^a , QoS Layer 3 DiffServ, FTP, CIFS/SMB, SMTP, Bonjour, UPnP TM , SNMP v1/v2c/v3 (MIB-II), DNS, DynDNS, NTP, RTSP, RTP, SFTP, TCP, UDP, IGMP, RTCP, ICMP, DHCP, ARP, SOCKS, SSH, NTCIP	Languages	English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Traditional Chinese
System integration		Warranty	Axis 3-year warranty and AXIS Extended Warranty option, see www.axis.com/warranty
Application Programming Interface	Open API for software integration, including VAPIX [®] and AXIS Camera Application Platform; specifications at www.axis.com AXIS Video Hosting System (AVHS) with One-Click Connection ONVIF Profile S, specification at www.onvif.org		
Analytics	Video motion detection, Autotracking, Active Gatekeeper Support for AXIS Camera Application Platform enabling installation of third-party applications, see www.axis.com/acap		
Event triggers	Analytics, Shock detection, Fan, Temperature, Manual trigger, PTZ moving, PTZ preset, Edge storage events Heater		
Event actions	File upload: FTP, SFTP, HTTP, HTTPS network share and email Notification: email, HTTP, HTTPS and TCP Day/night mode, Guard tour, Video recording to edge storage, Pre- and post-alarm video buffering, PTZ preset, Overlay text, Send SNMP trap		

- a. This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit. (www.openssl.org), and cryptographic software written by Eric Young (ey@cryptsoft.com).
b. Except valves on top

Environmental responsibility:

www.axis.com/environmental-responsibility