

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





TABLE - 1		
ASSEMBLY PART NUMBER	ITEM DESCRIPTION	WEIGHT
FSCBT2BU-X	OPTICAM 1.6/2.0mm CABLE RETENTION BOOT ASSEMBLY WITH BLUE BOOT	3.53g/10 Pcs [.125oz/10 Pcs]
FMCBT2AQ-X	OPTICAM 1.6/2.0mm CABLE RETENTION BOOT ASSEMBLY WITH AQUA BOOT	
FMCBT2BL-X	OPTICAM 1.6/2.0mm CABLE RETENTION BOOT ASSEMBLY WITH BLACK BOOT	

NOTES:

- SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
- SEE CATALOG FOR ADDITIONAL INFORMATION PERTAINING TO THESE PRODUCTS.
- 10 ASSEMBLIES PER PACKAGE.
- MATERIALS:
A. RETENTION NUT: PLASTIC
B. BOOT: RUBBER
- PRIMARY DIMENSIONS ARE METRIC,
DIMENSIONS IN [] ARE INCH.



PART NUMBER		FSCBT2** - X	
TITLE		OPTICAM 1.6/2.0mm CABLE RETENTION BOT ASSEMBLY	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		M01799AY/03	
MATERIAL:		PANDUIT	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		DRAWING NUMBER:	
.X ± .XX ±		.XXX ± ANGLES ±	
THIRD ANGLE PROJECTION		01799-45	
DRAWN BY	DATE	CHK	SCALE
MC	07-31-06	JAWI	NONE
SHT 1 OF 1			SIZE
			A

2	6/17/15	JSP	WJM	JGSW	A. REVISED DRAWING TITLE BLOCK.	01799-45
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

2

1

B

A

A

A

1