



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. APPLICATION TOOLS - GS4MT,PPTMT,ST2MT,ST3MT,HTMT
2. MINIMUM LOOP TENSILE STRENGTH - 200 LBS.[889 NEWTONS]
WHEN TESTED ON A 1.5" MANDREL.
3. BRACKETS [] DENOTE DIMENSIONS IN MILLIMETERS
AND ARE SHOWN FOR REFERENCE ONLY
4. TOLERANCES:
.XXX = $\pm .010$ [.25]
.XX = $\pm .02$ [.5]
.X = $\pm .03$ [.8]
ANGLES = $\pm 2^\circ$
5. MATERIAL: 316 STAINLESS STEEL

PANDUIT PART NO.	MAX BUNDLE DIAMETER	PACKAGE QTY	LENGTH L = $\pm .3$ [7]
MLT1S-CP316	1" [25]	100	5.0" [127]
MLT2S-CP316	2" [51]	100	7.9" [201]
MLT2.7S-CP316	2.7" [69]	100	10.2" [259]
MLT4S-CP316	4" [102]	100	14.3" [362]
MLT6S-CP316	6" [152]	100	20.5" [521]
MLT8S-CP316	8" [203]	100	26.8" [679]
MLT10S-CP316	10" [254]	100	33.0" [838]



							TITLE METAL LOCKING TIE STANDARD SERIES 316 STAINLESS STEEL CUSTOMER DRAWING					
							ITEM REVISION NAME N41120BS/10				PANDUIT	
							DATASET FILE NAME N41120BS_DC/010A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °  THIRD ANGLE PROJECTION					
							MATERIAL: 316 STAINLESS STEEL					
10	10.09.15	BDK	SKB	RGRO	A. ADDED NEW TIP CONFIGURATION	N41120BS_DC					DRAWING NUMBER: N41120BS_DC	
09A	3/13	JAMB	MIM	RGRO	UPDATE DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO	SSECN01037						
08A	2/12	MIM	RGRO	---	NOTE:#3 METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY	----						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE A
							JAMB	2/12	DPN	2:1		