


NOTES :

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. DIMENSIONS IN PARENTHESES ARE ENGLISH (in).
3. HEIGHT RANGE OF FLOOR SKIRT IS BETWEEN 31mm (1.2") AND 43.7mm (1.7") FROM THE FLOOR.
4. PARTS SUPPLIED:
 - (1)-FRONT OR REAR FLOOR SEAL
 - (1)-HARDWARE KIT
 - (1)-INSTRUCTION SHEET



PANDUIT PART NUMBER	"A" - LENGTH	PAINT COLOR	WEIGHT	CABINET TYPE	CABINET WIDTH
C2FAB06A1200B1	594.00 [23.386]	BLACK	0.8 Kg/EACH 1.76 LBS/EACH	S-TYPE	600mm
C2FAB07A1200B1	694.00 [27.323]	BLACK	0.9 Kg/EACH 1.98 LBS/EACH	S-TYPE	700mm
C2FAB08A1200B1	794.00 [31.260]	BLACK	1.0 Kg/EACH 2.20 LBS/EACH	N-TYPE OR S-TYPE	800mm

							<div>TITLE</div> <div>N & S-TYPE FRONT/REAR FLOOR SEAL CUSTOMER DRAWING</div> <div>CUSTOMER DRAWING</div> <div>ITEM REVISION NAME</div> <div>13V398ZH/00.PRT</div> <div>DATASET FILE NAME</div> <div>13V398ZH_DC/00A.PRT</div> <div>UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:</div> <div><div>INCHES</div><div>X.X +/- 0.03</div><div>X.XX +/- 0.018</div><div>X.XXX +/- 0.007</div></div> <div><div>METRIC - MILLIMETER</div><div>X. +/- 0.8</div><div>X.X +/- 0.46</div><div>X.XX +/- 0.18</div></div> <div><div>ANGLE</div><div>+/- 1°</div></div> <div>MATERIAL/COLOR:</div> <div>N/A</div> <div>DRAWING NUMBER:</div> <div>13V398ZH-DC</div>					
00A	2-04-14	PBS	RCHA	TCN	RELEASED TO PRODUCTION	13V398ZH-DC	<div><div><div><div></div></div><div><div></div></div></div><div>THIRD ANGLE PROJECTION</div></div> <div>DRAWING NUMBER:</div> <div>13V398ZH-DC</div>					
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							PBS	2-04-14	RCHA	NONE		A