

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. VISIT OUR ONLINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE WITH THIS PRODUCT.
2. REFER TO INSTRUCTION SHEET V00029LB FOR MORE INFORMATION
3. PARTS SUPPLIED:
 2 - TOP PANELS LH & RH
 2 - BOTTOM PANELS LH & RH
 4 - REVERSIBLE NOTCH COVERS
 4 - EXTENSION PANELS
 1 - HARDWARE KIT (NOT SHOWN)
 1 - INSTALLATION INSTRUCTION (NOT SHOWN).

PANDUIT PART NO.	WEIGHT
D6VBP*	4.5 Kg/EACH (9.92 LBS/EACH)

NOTE:

* DENOTES COLOR - ADD SUFFIX
 "B" FOR BLACK AND "W" FOR WHITE

TOP PANEL LH


TOP PANEL RH


REVERSIBLE
NOTCH COVER
TYP 4-PLCS

BOTTOM PANEL LH

BOTTOM PANEL RH




EXTENSION PANEL
TYP 4-PLCS
(45RU APPLICATIONS ONLY)

TITLE											
D-TYPE 600mm VERTICAL BLANKING PANEL (D6VBP*)											
CUSTOMER DRAWING											
ITEM REVISION NAME											
15V526ZQ/07											
DATASET FILE NAME											
15V526ZQ_DC/07A						MATERIAL:					
						N/A					
						DRAWING NUMBER:					
						15V526ZQ - DC					
DRAWN BY		DATE		CHK		SCALE		SIZE			
MES		1/11/17		DWR		NONE		SHT 1 OF 2			
								A			




THIRD ANGLE
PROJECTION

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



TOP VIEW

							TITLE	D-TYPE 600mm VERTICAL BLANKING PANEL (D6VBP*)					
							ITEM REVISION NAME	CUSTOMER DRAWING					
							DATASET FILE NAME	15V526ZQ/07					
								15V526ZQ_DC/07A					
								MATERIAL:					
								N/A					
								DRAWING NUMBER:					
								15V526ZQ-DC					
07A	1/12/17	MES	DWR	DWR	RELEASED TO PRODUCTION		V09001CM/05			THIRD ANGLE PROJECTION			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 2 OF 2		SIZE
							MES	1/12/17	DWR	NONE			A