


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	MATERIAL	"B" HEIGHT +/- .062	"C" IMPRINT AREA +/- .062	"D" VERTICAL REPEAT +/- .062	LABELS PER ROW	STANDARD PKG. QTY.
S100X075VA1Y	GM16 OR GM17	0.75 [ 19.1 ]	0.25 [ 6.35 ]	1.00 [ 25.4 ]	4	2500
S100X125VA1Y		1.25 [ 31.8 ]	0.38 [ 9.65 ]	1.50 [ 38.1 ]		
S100X150VA1Y		1.50 [ 38.1 ]	0.50 [ 12.7 ]	1.80 [ 45.7 ]		
S100X225VA1Y		2.25 [ 57.2 ]	0.75 [ 19.1 ]	2.50 [ 63.5 ]		1500
S100X250VA1Y		2.50 [ 63.5 ]	1.00 [ 25.4 ]	2.75 [ 69.8 ]		1000
S100X400VA1Y		4.00 [ 101.6 ]	1.00 [ 25.4 ]	4.25 [ 108.0 ]		
S100X650VA1Y		6.50 [ 165.1 ]	1.50 [ 38.1 ] +/- .10	6.75 [ 171.4 ]		250



9



NOTES:  
1. MILLIMETERS ARE IN [ ].

9	12/7/15	RVU	SEWH	JHAC	S100X650VA1Y WAS S100X600VA1Y.	GAECN03273
8	8/18/15	RVU	SEWH	JHAC	UPDATE ON NEW BOARDER WTIH PANDUIT LOGO.	GAECN03102
7	10/25/11	RVU			"GMV16 OR GMV17" WAS "GMV".	6548
6	12/10/09	RVU			GMV WAS GMV16. ADD +/- .10 TO 1.50.	5925
5	10/1/09	RVU			MILLIMETERS INCORRECT. [63.5] WAS [57.2], [9.65] WAS [9.53], [25.4] WAS [19.0], & [38.1] WAS [12.7].	5863
4	2/25/09	RVU			OBSOLETE PARTS: S***X***VA1, AND S***X***TA1. UPDATE TOLERANCE WITH +/- .062.	5682
3	6/13/08	RVU			VOID	5464
2	5/25/07	RVU			ADDED NEWPN, S100X225VA1Y.	5021
1	1/8/07	RVU			REVISED TOLERANCE.	4830
0	9/11/06	RVU			DRAWING RELEASED.	4671

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
-----	------	----	-----	-----	-------------	-----

TITLE					
S100X***VA1Y OPTIMUM SELF-LAMINATING THERMAL TRANSFER PRINTABLE LABELS CUSTOMER DRAWING					
ITEM REVISION NAME					
100472BS/13					
DATASET FILE NAME			MATERIAL:  SEE TABLE		
100472BS_DC_C10194/13K					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]  .x ± .12 [ 3.05 ]      .xxx ± .025 [ .635 ]  .xx ± .062 [ 1.57 ]      ANGLES ±			DRAWING NUMBER:  C10194		
 THIRD ANGLE PROJECTION					
DRAWN BY	DATE	CHK	SCALE	SIZE	
RVU	9/22/04	JHAC	NTS	SHT 1 OF 1	
				A	