


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	MATERIAL	PART DESCRIPTION	PRINT-ON HEIGHT "A" inches [mm] +/- .031	WIDTH inches [mm]	LENGTH inches [mm]	MIN. CABLE O.D. inches [mm]	MAX. CABLE O.D. inches [mm]	STD. PKG. CARDS	STD. CTN. CARDS
S100X125VARY	GMV3	(1) DISPENSER (1) ROLL, WHITE WRITE-ON VINYL LABEL, 200/ROLL (1) PUFX-0	0.375 [9.52]	1.00 [25.4]	1.25 [31.75]	0.12 [3.07]	0.28 [7.03]	1	10
S100X125VAFY		REFILL ROLLS: WHITE WRITE-ON, VINYL LABEL, 200/ ROLL							
S100X225VARY	GMV3	(1) DISPENSER (1) ROLL, WHITE WRITE-ON VINYL LABEL, 100/ROLL (1) PUFX-0	0.75 [19.05]	1.00 [25.4]	2.25 [57.15]	0.24 [6.06]	0.48 [12.13]	1	10
S100X225VAFY		REFILL ROLLS: WHITE WRITE-ON, VINYL LABEL, 100/ ROLL							

NOTES:
1. DIMENSION IN [] ARE IN MILLIMETERS.



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
2	11/28/16	RVU	SEWH	JHAC	REPLACE MARKING PEN, PFX-0 TO PUFX-0, SEE S100X125VARY AND S100X225VARY.	GAECN03871
1	3/30/11	RVU			ADD NEW ISO VIEW. UPDATE TABLE. REVISE TOLERANCES. REMOVE S100X***VAF AND VAR.	6338
0	1/25/07	RVU			DRAWING RELEASE.	4855

TITLE						
SELF-LAM. WIRE MARKER S100X***VARY AND S100X***VAFY CUSTOMER DRAWING						
ITEM REVISION NAME					100397HN/07	
DATASET FILE NAME					100397HN_DC_C10562/07C	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]					PANDUIT MATERIAL: SEE TABLE	
.x ± .12 [3.05] .xxx ± .015 [.381] .xx ± .062 [1.57] ANGLES ±						
DRAWN BY					DATE	CHK
RVU					1/25/07	JHAC
SCALE					THIRD ANGLE PROJECTION	
NTS					DRAWING NUMBER: C10562	
SHT 1 OF 1					SIZE A	