



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART NO.	MAX BUNDLE DIAMETER	PACKAGE QTY	LENGTH ("L") +/- .3" [7]
MLTFC2S-CP316	2" [51]	100	7.9" [201]
MLTFC4S-CP316	4" [102]	100	14.3" [361]
MLTFC6S-CP316	6" [152]	100	20.5" [521]
MLTFC8S-CP316	8" [203]	100	26.8" [679]



NOTES:

- 1.) APPLICATION TOOLS - GS4MT,PPTMT,ST2MT,ST3MT,HTMT
- 2.) MINIMUM LOOP TENSILE STRENGTH - 100 LBS. (445 NEWTONS) WHEN TESTED ON A 1.5" MANDREL.
- 3.) BRACKETS [] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
- 4.) TOLERANCES:
 - .XXX = ±.010 [.25]
 - .XX = ±.02 [.5]
 - .X = ±.03 [.8]
 - ANGLES = ±2°
- 5.) MATERIAL: 316 STAINLESS STEEL
- 6.) COATING - POLYESTER
COATING THICKNESS: .002 MIN./ .005 MAX.PER SIDE



							TITLE									
							METAL LOCKING TIE - COATED STANDARD SERIES									
							CUSTOMER DRAWING									
							ITEM REVISION NAME			N41214BS/03						
							DATASET FILE NAME			N41214BS/03						
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]					MATERIAL:				
							.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °					316 STAINLESS STEEL				
												DRAWING NUMBER:		N41214BS_DC		
							THIRD ANGLE PROJECTION									
03	08.27.15	BDK	SKB	RGRO	CHANGED BODY TIP CONFIGURATION	N41214BS_DC	DRAWN BY		DATE	CHK	SCALE	SHT 1 OF 1		SIZE		
							JAMB		8/05	EJD	2:1			A		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN										