



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. SEE SHEET 2 FOR PRODUCT DESCRIPTIONS AND TECHNICAL SPECIFICATIONS.
2. SEE CURRENT CATALOG FOR PATCH CORD LENGTHS AND PACKAGE QUANTITY.
3. FOR LENGTHS OTHER THAN THOSE LISTED IN CATALOG, CONTACT YOUR PANDUIT SALES PERSON.
4. TESTED TO EIA/TIA 568-B.3.
5. PATCH CORD ROUTING CONFIGURATION A TO B.
6. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

|     |          |    |     |                        |          |   |      |     |     |       |  |                                                                                                                    |                                                                                                                                                              |
|-----|----------|----|-----|------------------------|----------|---|------|-----|-----|-------|--|--------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------|
|     |          |    |     |                        |          |   |      |     |     |       |  | FIBER OPTIC PATCH CORD<br>DUPLEX ST TO ST CONFIGURATION<br>CUSTOMER DRAWING                                        |                                                                                                                                                              |
|     |          |    |     |                        |          |   |      |     |     |       |  |                               |  <sup>TM</sup><br>CORP.<br>TINLEY PARK, ILL 60477                       |
|     |          |    |     |                        |          |   |      |     |     |       |  |                                                                                                                    |                                                                                                                                                              |
|     |          |    |     |                        |          |   |      |     |     |       |  | <br>THIRD ANGLE<br>PROJECTION | ALL DIMENSIONS ARE GIVEN IN INCHES<br>UNLESS OTHERWISE SPECIFIED.<br><br>DIMENSIONAL TOLERANCES ARE:<br>(.X) (.XXX) ± .010 (0.3)<br>(.XX) ± .03 (0.8) ANGLES |
|     |          |    |     |                        |          |   |      |     |     |       |  |                                                                                                                    |                                                                                                                                                              |
|     |          |    |     |                        |          |   |      |     |     |       |  | DRAWN BY<br>MC                                                                                                     | REVIEW DRAWING NUMBERS                                                                                                                                       |
| R   | 06-05-07 | MC |     | RELEASED TO PRODUCTION | 02779-13 |   |      |     |     |       |  | DATE<br>04-27-07                                                                                                   | PART NO.<br>SEE TABLE, SHT. 2                                                                                                                                |
| REV | DATE     | BY | CHK | DESCRIPTION            | ECN      | R | CUST | SUP | OTH | CHK'D |  | DRAWING NO.<br>02779-13<br>(SHT. 1 of 2)                                                                           | SIZE<br>A                                                                                                                                                    |

