


NEC Ultra High Definition Large Format Displays

75", 86" and 98" Commercial Displays Ideal for Digital Signage Applications




Brand new UHD displays in an aesthetically-focused design allows for seamless integration into any digital signage environment while maintaining the commercial ruggedness necessary for the retail, educational and corporate environments

Beyond Standard Signage

With industry leading experience in superior design and customer focus, the NEC large C series allow for clear, detailed imagery for unobtrusive digital messaging. New contemporary and slim mechanical design with focused aesthetics allows for the smooth and stylistic integration into any type of environment. Their full metal chassis coupled with real-time temperature sensors and integrated cooling fans maintain the professional quality necessary for commercial environments. With an anti-glare screen and ultra high definition panel, customers can enjoy the perfect image in any circumstance. These displays come equipped with a wide range of the latest connectivity interfaces including three separate HDMI 2.0 interfaces, two separate DisplayPort interfaces and a DisplayPort Out connection to complement the native Ultra High Definition at 60Hz panel. These displays also include expandability options such as the Open Pluggable Specification (OPS) and Raspberry Pi Compute Module slots for source integration directly into the display. The NEC C series boasts 350 cd/m² brightness that allows for efficient readability in higher ambient light situations and is ideal for 24/7 signage in airports, quick-serve restaurants, and retail.


Scalable Computing Power

Integrated computing options allow for cable free signage for any type of situation. The on-board multimedia player can be utilized for simple signage applications by allowing auto-play off of USB or SD card and content transfer via LAN. For more advanced signage systems, these displays contain an industry first ability to integrate a Raspberry Pi Compute module for near limitless potential and application. Finally, each display adheres to the Open Pluggable Specification that gives the ability to seamlessly integrate a full PC, HDBaseT receiver or other options directly into the unit.



Advanced Heat Management

Monitoring and managing the temperature of each display is crucial to secure reliability and longevity. An industrial-strength, premium-grade panel with additional thermal protection, internal temperature sensors with self-diagnostics, and fan-based technology allows for 24/7 operation, and protects your display investment. Without thermal management, displays can be prone to damaging heat over time. This damaging heat will lower the picture quality and life expectancy of the product. Integrated cooling fans automatically turn on and stay on when high internal temperatures are detected. These will stay on until the heat is properly dissipated and the display remains under proper temperature thresholds.



Location of Thermal Management Cooling Fans



Anti-Glare Panel

Each of the new large C series commercial displays come equipped with a high haze panel that scatters ambient lighting rather than reflecting it like most other displays. This allows for content to always be viewable and onlookers to have perfect screen readability in any situation.



With Anti-Glare



Without Anti-Glare

Blue ON LED and Ambient Light Sensor

New mechanical structure allows for sleeker LED and ambient light sensor design. Auto dimming of the LED backlights can be utilized through the ambient light sensor allowing for the brightness to change depending on the external lux in the room of installation.




SpectraView Engine

Enhanced imaging performance through advanced settings of all relevant parameters allow full control of brightness, color, gamma and uniformity via integrated color-critical chipset.



Key Guide

New Key Guide function allows for easier access to buttons when manually controlling the unit via the buttons on the back of the display by adding a graphic on the screen that directs the customer to the correct button layout in both landscape and portrait modes.



Aesthetically Focused Design

Brand new mechanical design focuses on smooth, sleek curves, thinner bezels, reduced depth and reduced overall weight while maintaining the quality and reliability for efficient 24/7 runtime capabilities.




NaViSet Administrator 2

This software is an all-in-one remote support solution that runs from a central location and provides monitoring, asset management and control functionality of the majority of NEC display devices and Windows computers. It is ideal for multi-device installations over larger infrastructures.



L-Shaped Connectivity

Connectivity is located on both the bottom and side of the display to allow for easy access regardless of orientation



Intelligent Wireless Data Function

The built-in near field communication (NFC) chip allows data to be read and written via a mobile phone or tablet PC. Users can significantly reduce installation costs as displays can be easily configured and serviced using the NEC NFCAndroid app. This is extremely useful for larger rollouts as it can be utilized even when the display is powered off.




Removable Logo


When mounting from Landscape to Portrait orientation, there is now the ability to change the orientation of the logo or remove it all together



MODEL		C751Q	C861Q	C981Q
LCD MODULE	Panel Technology	E-LED, S-IPS		D-LED, S-IPS
	Viewable Image Size	75"	86"	98"
	Native Resolution	3840 x 2160		
	Brightness (Typical/Maximum)	245 cd/m ² / 350 cd/m ²		
	Contrast Ratio (Typical)	1200:1 native, not including localized dimming		1300:1 native, not including localized dimming
	Viewing Angle	178° Vert., 178° Hor. (89U/89D/89L/89R) @ CR>10		
	Aspect Ratio	16:9		
	Displayable Colors	Over 1.07 Billion		
	Orientation	Landscape and Portrait		
	Panel Haze (%)	28		
CONNECTIVITY	Input Terminals			
	Digital	HDMI 2.0 x3 (with HDCP), DisplayPort 1.2 x2 (with HDCP)		
	Analog	None		
	Audio	3.5mm Mini Jack, HDMI Audio x3, DisplayPort Audio x2		
	External Control	LAN (100Mbit), 3.5 Mini Jack IR Remote, RS232C		
	Data	microSD (Media Player), USB 2.0 (Media Player), USB 2.0 (Service), USB Type-B (Upstream), USB 2.0 x2 (Compute Module, USB CM1 is Powered 5V/2A)		
	Output Terminals			
	Digital	DisplayPort (Outputs DisplayPort1 and OPS (1CH DisplayPort Only))		
	Analog	None		
	Audio	3.5mm Audio Mini Jack, External Speaker Jack x2		
POWER CONSUMPTION	External Control	LAN (100Mb)		
	On (Typ/Max Brightness/Overall Max)	195W/250W/375W	230W/300W/425W	240W/380W/525W
	Network Standby	2W		
	Normal Standby	0.5W		
	Current Rating	4.4A @ 100V, 1.9A @ 240V	5.0A @ 100V, 2.1A @ 240V	6.1A @ 100V, 2.6A @ 240V
	Speaker Rating	Integrated 10W x 2, Optional 15W x 2		
PHYSICAL SPECIFICATIONS	Bezel Width (L/R, T/B)	14.8mm/14.8mm/ 14.8mm/14.8mm	15.3mm/15.3mm/ 15.3mm/15.3mm	15.9mm/15.9mm/ 15.9mm/15.9mm
	Net Dimensions (Without stand; W x H x D)	66.2 x 37.8 x 2.8in. 1681.2 x 959.6 x 71.1mm	75.9 x 43.3 x 2.9in. 1928.2 x 1099.2 x 74.3mm	86.4 x 49.2 x 3.7in. 2193.8 x 1248.8 x 93.0mm
	Net Weight (Without Stand)	115.7lbs. / 52.6kg	127.2 lbs. / 57.8kg	198.6 lbs. / 90.0kg
	VESA Hole Configuration	8x M8 x 16mm (600 x 400, 400 x 400)		
	Ambient Light Sensor	Integrated and programmable		
SENSORS	Human Sensor	Optional through KT-RC2 Accessory		
	Temperature Sensor	Integrated and programmable; linked to cooling fans		
	NFC Sensor	Integrated; works in conjunction with free NEC Intelligent Wireless Data Application		
ENVIRONMENTAL CONDITIONS	Operating Temperature	0 to 40C		
	Operating Humidity	20-80%		
	Operating Altitude	3000m (9843ft)		
LIMITED WARRANTY		3 years Advanced Replacement		
ADDITIONAL FEATURES		HDR Gamma Support (HLG and PQ), Localized Dimming, Ambient Light Sensor, AMX Support, Auto ID/Auto TileMatrix, Automated Email Alert Function, CEC Support through HDMI, Crestron Roomview Support, DICOM Simulation, Display Browser Control, Display Wall Calibrator Compatible, High Haze Panel, Image Flip, Intelligent Wireless Data (NFC), Key Guide, Media Player through Browser Control/SD Card/USB, Multi Picture Mode, Naviset Administrator 2 Compatible, OSD Rotation for Portrait Orientation, OPS Compatible, PJ Link Support, Point Zoom Function, Power USB Port (5V/2A), Programmable LUT x3, Raspberry Pi Compute Module Compatible, Removable Logo Ornament, Real Time Clock, SpectraView Engine Support, SNMP Support, 24-Hour Scheduler Function		
SHIPS WITH		3m AC Power Cord, 1.8m HDMI cable, 1.8m DisplayPort Cable, IR Remote Control, Batteries, CD-ROM (User Manual)		
OPTIONAL ACCESSORIES		Table Top Stand (ST-801), Optional Speakers (SP-TF1), All OPS Option Cards, Raspberry Pi Compute Module 1 and 3 with optional NEC Interface Board, Large Wall Mount (WMK-6598), Regular Wall Mount (WMK-3257 for V754Q, and V864Q only) Slim Wall Mount (WMK-3255S for V754Q/V864Q), Human Sensor (KT-RC2)		



Dimensions



Options

OPS PC's

OPS-PCAEQ-PS2

OPS-APIS-PS

OPS-TCIS-PS



SDI

HD-SDI

3G-SDI

SB-01HC

SB-04HC



HDBaseT

SB-07BC



Compute Module

Compute Module Interface Board

NEC Raspberry Pi Compute Module

DS1-IF10CE

RP3CM16GB




Tabletop Stand

ST-801



Speaker

SP-TF1



Input Panels

- | | |
|-------------------------------------|---------------|
| 1. HDMI IN2 | 13. USB CM2 |
| 2. HDMI IN3 | 14. LAN1 |
| 3. DisplayPort IN2 | 15. LAN2 |
| 4. DisplayPort IN1 | 16. USB MP |
| 5. DisplayPort OUT | 17. microSD |
| 6. Audio IN | 18. REMOTE IN |
| 7. External Speaker Terminal | 19. RS-232C |
| 8. Internal/External Speaker Switch | 20. HDMI IN1 |
| 9. Audio OUT | |
| 10. USB1 | |
| 11. USB2 | |
| 12. USB CM1 (2A) | |

MultiSync, Naviset and TileMatrix are trademarks or registered trademarks of NEC Display Solutions, Ltd. in Japan, the United States and other countries. The terms HDMI and HDMI High-Definition Multimedia Interface, and the HDMI Logo are trademarks or registered trademarks of HDMI Licensing LLC in the United States and other countries. DisplayPort and DisplayPort Compliance Logo are trademarks owned by the Video Electronics Standards Association in the United States and other countries.

HDBaseT™ and the HDBaseT Alliance logo are trademarks of the HDBaseT Alliance.

CRESTRON and CRESTRON ROOMVIEW are trademarks or registered trademarks of Crestron Electronics, Inc.

AMX is a trademark or registered trademark of AMX in the United States and other countries.

VESA is a trademark of a nonprofit organization, Video Electronics Standard Association.

All other trademarks are the property of their respective owners. The images in this brochure are samples.

All specifications are subject to change without notice.

©2018 NEC Display Solutions of America, Inc. and the NEC logo are registered trademarks of NEC.



www.necdisplay.com

Cat.No. 25.NEC.80.GL.UN.321 05.31.2018