

DRAWING NO. SD035209		7			6		5			4			3			2			1														
CATALOG NUMBER	STRANDED COPPER CONDUCTOR ACCOMMODATED			BOLT SIZE	METRIC BOLT SIZE	DIMENSIONS								REV C 06/18/2011 00:00:00 AM			DATE			DESCRIPTION			ECO 24861	BY AD	C'H'K. MA								
	CODE (AWG)	NAVY	METRIC SIZE (CLASS 2)			B	C	E	K DIA.	L	N	O.D.	T MIN.	Z MIN.	TOLERANCES																		
YA30L2TC14E1	250 kcmil	250	120mm ² STR [14.5]	1/4	M6	1.06 [27]	1.20 [30]	1.00 [25]	.27 [7]	3.26 [83]	.31 [8]	.81 [19]	.16 [4]	.33 [8]	-8C THRU -25	±.06	±.04	±.02	±.02	±.09	±.03	±.01											
YA292L				3/8	M10	1.10 [28]	1.06 [27]	.41 [10]	3.50 [89]	.41 [10]	.75 [19]	.42 [11]	-26 THRU -34	±.08		±.04	±.02	±.02	±.12	±.03	±.01												
YA29L2TC38				3/8	M10	1.10 [28]	1.00 [25]	.41 [10]	3.43 [87]	.41 [10]	.75 [19]	.42 [11]		-35 AND UP		±.09	±.06	±.02	±.02	±.15	±.06	±.01											
YA29L2TC38E10				3/8	M10	1.10 [28]	1.25 [32]	.41 [10]	3.68 [93]	.41 [10]	.75 [19]	.42 [11]																					
YA292LN				1/2	M12	1.06 [27]	1.10 [28]	1.75 [44]	.56 [14]	4.62 [117]	.63 [16]	.75 [19]				.64 [16]																	
YA29L2TC14E1	300 kcmil	300	150mm ² STR [16.2]	1/4	M6	1.03 [26]	1.10 [28]	1.00 [25]	.27 [7]	3.25 [83]	.31 [8]	.75 [19]			.33 [8]	TOLERANCE BLOCK																	
YA302L				3/8	M21	1.20 [30]	1.06 [27]	.41 [10]	3.51 [89]	.41 [10]	.81 [21]	.42 [11]																					
YA30L2TC38				3/8	M12	1.20 [30]	1.00 [25]	.41 [10]	3.45 [87]	.41 [10]	.81 [21]	.42 [11]																					
YA302LN				1/2	M12	1.03 [26]	1.20 [30]	1.75 [44]	.56 [14]	4.63 [118]	.63 [16]	.81 [21]	.64 [16]																				
INSTALLATION TOOLING (# CRIMPS)																																	
CATALOG NO.	COLOR CODE	DIE INFORMATION		MECHANICAL				HYDRAULIC						DIELESS (# CRIMPS)	WIRE STRIP LENGTH																		
		DIE INDEX	TYPE	YIMRTC 6	OUR840	MD6 MD7	MD6--R2 MD7-34R	Y34A Y34B Y34BH 8	Y35, Y39 Y750, PAT750 5	Y46 PAT46 4 5	Y45 3 5	Y48B	Y60BHU																				
YA29- SERIES	YELLOW	16	YELLOW DIE SET	-----	X29RT(4)	W29VT(2)	W29RT(2) W29VT(2)	A29R(1)	U29RT(1)	U29RT(1)	U29RT(1)	C29R(1)	L29RT(1)	MECHANICAL: MY29-3(1) MY29-11(1) HYDRAULIC: Y81KFT(2) Y4PC834(2) Y644(1)	1-1/8"																		
			NEST	-----	-----	-----	B29D(1) A29D(1)	U29D-1(1)	U29D-1(1)	U29D-1(1)	C29D(1)	-----																					
			INDENTOR	-----	-----	-----	Y34PR	Y34PR	Y34PR	Y34PR	Y48PR	-----																					
YA30- SERIES	WHITE	17 298	WHITE DIE SET	-----	-----	-----	W30RT(2)	A28AR(1)	U30RT(2) U28ART(2)	U30RT(2) U28ART(2)	U30RT(2) U28ART(2)	C30R(2) C28AR(2)	L30RT(1)	HYDRAULIC: Y81KFT(2) Y4PC834(2) Y644(1)	1"																		
			NEST	-----	-----	-----	B30D(1) A30D(1)	U30D-1(1)	U30D-1(1)	U30D-1(1)	C30D(1)	-----																					
			INDENTOR	-----	-----	-----	Y34PR	Y34PR	Y34PR	Y34PR	Y48PR	-----																					
NOTES:																TO ORDER BURNDY® PRODUCTS CALL									HYLUG™ (COPPER)								
1. MATERIAL: COPPER TUBING.																UNITED STATES									ITEM NO: N/A								
2. FINISH: TIN PLATED.																1-800-346-4175 (LONDONDERRY, NH)									CAT. NO: YA--2L-, YA--2TC- (TABLE)								
3. CATALOG # PT6515 ADAPTOR IS REQUIRED TO USE "U" DIES IN Y45 SERIES TOOLS.																CANADA:									DRAWN BY: J.MICHAUD 11/18/94								
4. CATALOG # PUADP-1 ADAPTOR IS REQUIRED TO USE "U" DIES IN Y46 SERIES TOOLS.																1-800-361-6975 (QUEBEC)									CHECKER: D.FILLION 11/18/94								
5. Y35P3 INDENTOR ADAPTOR REQUIRED FOR Y34PR INDENTOR.																1-800-387-6487 (ALL OTHER PROVINCES)									DSN APPVL: C.PALAGI 10/24/94								
6. PERMANENT DIE IN TOOLING.																FOR PRODUCT INFO: http://www.burndy.com									MFG APPVL: -- --								
7. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.																									QA APPVL: C.ACKERMAN 11/17/94								
FOR USE BY CUSTOMERS THAT HAVE THIS HYPRESS™. NO NEW Y34A HYPRESS™ TOOLS ARE BEING PROCESSED. Y34A USES A--D TYPE NEST DIES.																									MKT APPVL: T.NELSON 11/10/94								
9. CONNECTORS ARE UL LISTED; UNDRILLED VERSIONS ARE NOT UL LISTED.																									PROD FAM: CM&R COMPRESSION								
10. CONNECTORS ARE CSA CERTIFIED; UNDRILLED VERSIONS ARE NOT CSA CERTIFIED.																									SCALE: NTS								
11. FOR UNDRILLED VERSIONS ADD SUFFIX "-U" TO END OF CATALOG NUMBER. FOR UNDRILLED VERSIONS, USE D MIN. = N MAX. + E MIN. + Z MIN.																									DRAWING NO								
12. "X", "W-RT", "W-VT", "U", & "L" DIE SETS ARE COLOR CODED. "A", "B", AND "C" DIES ARE NOT COLOR CODED. NESTS AND INDENTOR TYPE ARE NOT COLOR CODED.																									SD035209								
																									SHEET 9 OF 18								
																									C								